




SERIES 70 10K PSI / 700 BAR / 7000 M



SeaKing™ High-Pressure Subsea Connectors, Cables, and PBOF Assemblies

709-154 Pressure Cap for Reverse Gender Plug

SeaKing - How To Order				
Sample Part Number	709-154	-K19	-Z1	L
Product Series	709-154 = Pressure Cap for Reverse Gender SeaKing Plug, PBOF Applications			
Shell Size/Insert Arrangements	See Dimensions Table			
Body Material	Z1 = Stainless Steel* TC = Titanium			
Lanyard Option	(Leave Blank For No Lanyard)			




NOTES

Mates to reverse gender seaking cable connector plug (CCP) 707-0147-1 of same size and contact arrangement.
For PBOF applications, this pressure cap provides environmental and pressure barrier to 10,000 psi.

MATERIAL COMPOSITION:

- Body: see part number development
- Pressure pad: glass-reinforced polyetherimide
- O-ring: nitrile, 90 durometer
- Lanyard: fep coated stainless steel rope
- Lanyard crimp sleeves: stainless steel



Dimensions				
Shell Size	Hex H		Thread T	O-Ring Size
	In.	mm		
G	.937	23.80	15/16-12 UN-2A	2-014
K	1.062	26.97	11/16-12 UN-2A	2-016
L	1.187	30.15	13/16-12 UN-2A	2-018
M	1.312	33.32	15/16-12 UN-2A	2-019
O	1.562	39.67	19/16-12 UN-2A	2-023
P	1.687	42.85	1 11/16-12 UN-2A	2-025
Q	1.812	46.02	1 13/16-12 UN-2A	2-028
R	1.937	49.20	1 15/16-12 UN-2A	2-029

