




SERIES 70 10K PSI / 700 BAR / 7000 M



SeaKing™ High-Pressure Subsea Connectors, Cables, and PBOF Assemblies

709-159 Reverse Gender PEEK Pressure Cap for Plug

SeaKing - How To Order					
Sample Part Number	709-159	-M	12	-L	
Product Series	709-159 = Reverse Gender PEEK Pressure Cap for SeaKing Plug				
SeaKing Plug Size	See Dimensions table				
Arrangement	See Dimensions table				
Lanyard Option	(Leave Blank For No Lanyard)				




NOTES

Mates to reverse gender seaking cable connector plug (CCP) 707-0147-1 of same size and contact arrangement.
For PBOF applications, this pressure cap provides environmental and pressure barrier to 10,000 psi.

MATERIAL COMPOSITION:

- Body: see part number development
- Pressure pad: glass-reinforced polyetherimide
- O-ring: nitrile, 90 durometer
- Lanyard: fep coated stainless steel rope
- Lanyard crimp sleeves: stainless steel



Dimensions						
Size	H		T Threads	L		O-Ring Size
	In.	mm		In.	mm	
G	.938	23.83	15/16-12 UN-2A	1.020	25.91	2-014
K	1.063	27.00	1 1/16-12 UN-2A	1.020	25.91	2-016
L	1.188	30.18	1 3/16-12 UN-2A	1.020	25.91	2-018
M	1.313	33.35	1 5/16-12 UN-2A	1.075	27.31	2-019
O	1.563	39.70	1 9/16-12 UN-2A	1.185	30.10	2-023
P	1.688	42.88	1 11/16-12 UN-2A	1.240	31.50	2-025
Q	1.813	46.05	1 13/16-12 UN-2A	1.295	32.89	2-028
R	1.938	49.23	1 15/16-12 UN-2A	1.350	34.29	2-029