



SERIES 70 10K PSI / 700 BAR / 7000 M SeaKing™ High-Pressure Subsea Connectors, Cables, and PBOF Assemblies 709-162 PEEK Pressure Cap for Plug





SeaKing - How To Order			
Sample Part Number	709-162	-M	-L
Product Series	709-162 = PEEK Pressure Cap for Seaking Plug		
SeaKing Plug Size	See Dimensions Table		
Lanyard Option	Leave Blank for No Lanyard		

NOTES

Mates to SeaKing peek cable connector plug (ccp) 707-0150-1.
Provides environmental protection to 10,000 psi.

MATERIAL COMPOSITION:

- Body: 30% glass-reinforced P.E.E.K.
- O-ring: nitrile rubber, 90 durometer
- Lanyard: fep coated stainless steel rope
- Lanyard crimp sleeves: stainless steel



OPTIONAL LANYARD IS SECURED TO THE CAP AND SEAKING PLUG ASSEMBLY AT THE FACTORY.

Size	Hex		Threads	Length		O-Ring Size
	In.	mm		In.	mm	
E	.813	20.65	13/16-12 UN-2A	1.020	25.91	2-012
G	.938	23.83	15/16-12 UN-2A	1.020	25.91	2-014
K	1.063	27.00	1 1/16-12 UN-2A	1.020	25.91	2-016
L	1.188	30.18	1 3/16-12 UN-2A	1.020	25.91	2-018
M	1.313	33.35	1 5/16-12 UN-2A	1.075	27.31	2-019
O	1.563	39.70	1 9/16-12 UN-2A	1.185	30.10	2-023
P	1.688	42.88	1 11/16-12 UN-2A	1.240	31.50	2-025
Q	1.813	46.05	1 13/16-12 UN-2A	1.295	32.89	2-028
R	1.938	49.23	1 15/16-12 UN-2A	1.350	34.29	2-029

