Glenair®

930-006
Gasket for MIL-C-28840 Connectors

930 - 006 F 13

- Product Series
- Basic Number
- Material Symbol (Table II)
- Shell Size (Table I)



NOTES:

1. Identified by bag and tag in suitable quantities.
2. Metric dimensions (mm) are indicated in parentheses.

© 2005 Glenair, Inc.

930-006
Gasket for MIL-C-28840 Connectors

TABLE I: SHELL SIZE

Shell Size MIL-C-28840	A ±.010	(0.3)	B Dia +.016 -.0	(+0.4 -0)	C +.016 -.0	(+0.4 -0)	D Dia ±.010	(0.3)	F Radius ±.010	(0.3)
11	.750	(19.1)	.750	(19.1)	1.023	(26.0)	.120	(3.0)	.141	(3.6)
13	.843	(21.4)	.875	(22.2)	1.138	(28.9)	.120	(3.0)	.141	(3.6)
15	.968	(24.6)	1.062	(27.0)	1.258	(32.0)	.120	(3.0)	.141	(3.6)
17	1.015	(25.8)	1.125	(28.6)	1.383	(35.1)	.120	(3.0)	.156	(4.0)
19	1.140	(29.0)	1.312	(33.3)	1.508	(38.3)	.120	(3.0)	.172	(4.4)
23	1.281	(32.5)	1.500	(38.1)	1.718	(43.6)	.120	(3.0)	.188	(4.8)
25	1.392	(35.4)	1.625	(41.3)	1.818	(46.2)	.147	(3.7)	.188	(4.8)
29	1.568	(39.2)	1.875	(47.6)	2.138	(54.3)	.147	(3.7)	.219	(5.6)
33	1.734	(44.0)	2.062	(52.4)	2.328	(59.1)	.173	(4.4)	.219	(5.6)

TABLE II: MATERIAL

Symbol	Material Description
F	Fluorosilicone
M	Conductive — Con-Sil II
N	Neoprene

Metric Dimensions (mm) are indicated in parenthesis.

© 2005 Glenair, Inc.