

Ordering Information: El Ochito[®] White Contacts, Type I



EL OCHITO[®] CONTACT ORDERING INFORMATION

El Ochito[®] Contacts: How To Order



Data Protocol: Cat 6A up to 10G, Cat 8 up to 40G Ethernet
El Ochito[®] White

Connector Type	Protocol	Wire Size	Cable Type	Recommended Cable		El Ochito [®] Type I	
				Glenair Part No.	Cable Dia.	Pin Contact <i>Assembly Instr.</i>	Skt Contact <i>Assembly Instr.</i>
• ARINC 600 <i>Type I Contacts</i>	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-009-01 AI85074-01	858-010-01 AI85074-01
	Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-009-02 AI85084-01	858-010-02 AI85084-01
	Cat 6A	28	S/FTP	963-033-28	.177 (4.50)	858-009-03 AI85084-03	858-010-03 AI85084-03
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-009-04 AI85084-04	858-010-04 AI85084-04
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-009-05 AI85084-05	858-010-05 AI85084-05
• EN3645 • EN4165 <i>Type I Contacts</i>	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-026-01 AI85048-01	858-027-01 AI85048-01
	Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-026-02 AI85048-02	858-027-02 AI85048-02
	Cat 6A	28	S/FTP	963-033-28	.177 (4.50)	858-026-03 AI85048-03	858-027-03 AI85048-03
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-026-04 AI85048-04	858-027-04 AI85048-04
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-026-05 AI85048-05	858-027-05 AI85048-05
• Radial EPXB <i>Type I Contacts</i>	Cat 6A	26	S/UTP	963-033-26	.220 (5.59)	858-014-01 AI85105-01	858-015-01 AI85105-01
	Cat 6A	26	S/FTP	963-003-26	.220 (5.59)	858-014-02 AI85105-01	858-015-02 AI85105-02
	Cat 6A	28	S/FTP	963-033-28	.177 (4.50)	858-014-03 AI85105-03	858-015-03 AI85105-03
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-014-04 AI85105-04	858-015-04 AI85105-04
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-014-05 AI85105-05	858-015-05 AI85105-06

Ordering Information: El Ochito® White Contacts, Type I

El Ochito® Contacts: How To Order								
		Data Protocol: Cat 6A up to 10G, Cat 8 up to 40G Ethernet El Ochito® White						
		Connector Type	Protocol	Wire Size	Cable Type	Recommended Cable		El Ochito® Type I
					Glenair Part No.	Cable Dia.	Pin Contact Assembly Instr.	Skt Contact Assembly Instr.
<ul style="list-style-type: none"> • EN3545 	Type I Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-055-01 A185194-01P	858-056-01 A185194-01S
		Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-055-02 A185194-02P	858-056-02 A185194-02S
		Cat 6A	28	S/FTP	963-033-28	.177 (4.50)	858-055-03 A185194-03P	858-056-03 A185194-03S
		Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-055-04 A185194-04P	858-056-04 A185194-04S
		Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-055-05 A185194-05P	858-056-05 A185194-05S
<ul style="list-style-type: none"> • SuperNine® (Series 23) • HiPer-D® (Series 28) 	Type I Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-003-01F A185048-01	858-004-01F A185048-01
		Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-003-02F A185048-02	858-004-02F A185048-02
		Cat 6A	28	S/FTP	963-033-28	.177 (4.50)	858-003-03F A185048-03	858-004-03F A185048-03
		Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-003-04F A185048-04	858-004-04F A185048-04
		Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-003-05F A185048-05	858-004-05F A185048-05
<ul style="list-style-type: none"> • Series 792 • Series 806 • Series 816 	Type I Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-045-01F A185151-01	858-046-01F A185151-01
		Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-045-02F A185151-02	858-046-02F A185151-02
		Cat 6A	28	S/FTP	963-033-28	.177 (4.50)	858-045-03F A185151-03	858-046-03F A185151-03
		Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-045-04F A185151-04	858-046-04F A185151-04
		Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-045-05F A185151-05	858-046-05F A185151-05

EL OCHITO® CONTACT ORDERING INFORMATION