


Ordering Information: El Ochito[®] White Contacts, Type II



EL OCHITO[®] CONTACT ORDERING INFORMATION


El Ochito[®] Contacts: How To Order



Data Protocol: Cat 6A up to 10G, Cat 8 up to 40G Ethernet
El Ochito[®] White

Connector Type	Protocol	Wire Size	Cable Type	Recommended Cable		El Ochito [®] Type II	
				Glenair Part No.	Cable Dia.	Pin Contact Assembly Instr.	Skt Contact Assembly Instr.
• EN3545 Type II Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-061-01 A185193-01P	858-062-01 A185193-01S
	Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-061-02 A185193-02P	858-062-02 A185193-02S
	Cat 6A	24	S/UTP	963-037-24	.260 (6.60)	858-061-03 A185193-03P	858-062-03 A185193-03S
	Cat 6A	24	S/FTP	963-033-24	.260 (6.60)	858-061-04 A185193-04P	858-062-04 A185193-04S
	Cat 6A	24	S/UTP	963-003-24	.280 (7.11)	858-061-05 A185193-05P	858-062-05 A185193-05S
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-061-06 A185193-06P	858-062-06 A185193-06S
	Cat 8	24	S/FTP	963-132-24	.260 (6.60)	858-061-07 A185193-07P	858-062-07 A185193-07S
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-061-08 A185193-08P	858-062-08 A185193-08S
• SuperNine [®] (Series 23) • HiPer-D [®] (Series 28) Type II Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-005-01 A185097-01	858-006-01 A185097-01
	Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-005-02 A185097-02	858-006-02 A185097-02
	Cat 6A	24	S/UTP	963-037-24	.260 (6.60)	858-005-03 A185097-03	858-006-03 A185097-03
	Cat 6A	24	S/FTP	963-033-24	.260 (6.60)	858-005-04 A185097-04	858-006-04 A185097-04
	Cat 6A	24	S/UTP	963-003-24	.280 (7.11)	858-005-05 A185097-05	858-006-05 A185097-05
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-005-06 A185097-06	858-006-06 A185097-06
	Cat 8	24	S/FTP	963-132-24	.260 (6.60)	858-005-07 A185097-07	858-006-07 A185097-07
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-005-08 A185097-08	858-006-08 A185097-08

Ordering Information: El Ochito® White Contacts, Type II

El Ochito® Contacts: How To Order							
 Data Protocol: Cat 6A up to 10G, Cat 8 up to 40G Ethernet El Ochito® White							
Connector Type	Protocol	Wire Size	Cable Type	Recommended Cable		El Ochito® Type II	
				Glenair Part No.	Cable Dia.	Pin Contact Assembly Instr.	Skt Contact Assembly Instr.
• Series 792 Type II Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-043-01 A185134-01	858-042-01 A185134-02
	Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-043-02 A185134-02	858-042-02 A185134-02
	Cat 6A	24	S/UTP	963-037-24	.260 (6.60)	858-043-03 A185134-02	858-042-03 A185134-02
	Cat 6A	24	S/FTP	963-033-24	.260 (6.60)	858-043-04 A185134-04	858-042-04 A185134-04
	Cat 6A	24	S/UTP	963-003-24	.280 (7.11)	858-043-05 A185134-05	858-042-05 A185134-05
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-043-06 A185134-06	858-042-06 A185134-06
	Cat 8	24	S/FTP	963-132-24	.260 (6.60)	858-043-07 A185134-07	858-042-07 A185134-07
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-043-08 A185134-08	858-042-08 A185134-08
• Series 806 • Series 816 Type II Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-051-01 A185149-01	858-052-01 A185149-02
	Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-051-02 A185149-02	858-052-02 A185149-02
	Cat 6A	24	S/UTP	963-037-24	.260 (6.60)	858-051-03 A185149-03	858-052-03 A185149-03
	Cat 6A	24	S/FTP	963-033-24	.260 (6.60)	858-051-04 A185149-04	858-052-04 A185149-04
	Cat 6A	24	S/UTP	963-003-24	.280 (7.11)	858-051-05 A185149-05	858-052-05 A185149-05
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-051-06 A185149-06	858-052-06 A185149-06
	Cat 8	24	S/FTP	963-132-24	.260 (6.60)	858-051-07 A185149-07	858-052-07 A185149-07
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-051-08 A185149-08	858-052-08 A185149-08

EL OCHITO® CONTACT ORDERING INFORMATION