

SuperNine® RJ45 CAT 5e and 6A MIL-DTL-38999 Series III Type connectors Product Selection Guide



RJ45 CAT 5E AND 6A CONNECTORS

 <p>233-312 E-9 SuperSeal™ CAT 6A Plug with RJ45 Male Mating Interface and Accessory Threads</p>	 <p>233-330 E-22 SuperSeal™ CAT 5e and 6A Feed-thru Receptacle with Jack-to-Jack RJ45.</p>
 <p>233-300 E-10 SuperSeal D38999 Type plug with CAT 5e or 6A RJ45 Plug or D38999 Type Receptacle with CAT 5e or 6A RJ45 Jack. D38999 Type Shells with Accessory Threads</p>	 <p>Cable Assemblies E-24 SuperSeal™ CAT 5e Cable Assemblies</p>
 <p>233-301 E-12 SuperSeal™ CAT 5e Receptacle Adapter with RJ45 Mating Interface and Crimp Removable Contacts.</p>	 <p>Transient Voltage Suppression (TVS) RJ45 Connectors E-25 Prevents Catastrophic EMP Failure in Military and Commercial Aircraft</p>
 <p>233-302 E-14 SuperSeal™ CAT 5e Receptacle with RJ45 Mating Interface and PC Tail Termination.</p>	 <p>244-001 E-27 SuperSeal™ CAT 5e Transient Voltage Suppression, Jam-Nut Receptacle with Standoffs and RJ45 Jack to PC Tail or Solder Cup Termination.</p>
 <p>233-303 E-16 SuperSeal™ CAT 5e Receptacle with RJ45 Mating Interface and Solder Cup Termination.</p>	 <p>244-002 E-28 SuperSeal™ CAT 5e Transient Voltage Suppression, Wall Mount Receptacle with Standoffs and RJ45 Jack, Mating Interface to PC Tail or Solder Cup.</p>
 <p>233-304 E-18 SuperSeal™ CAT 5e MIL-STD-1560 Interface Receptacle Adapter with Accessory Threads and Rear RJ45 Jack.</p>	 <p>244-003 E-29 SuperSeal™ CAT 5e Transient Voltage Suppression Jam-Nut Receptacle with Accessory Threads and RJ45 Jack, Mating Interface to PC Tail or Solder Cup.</p>
 <p>233-305 E-20 SuperSeal™ CAT 5e Quadrax Interface Receptacle Adapter with Accessory Threads and Rear RJ45 Jack.</p>	 <p>244-004 E-30 SuperSeal™ CAT 5e Transient Voltage Suppression Wall Mount Receptacle with Accessory Threads and RJ45 Jack, Mating Interface to PC Tail or Solder Cup.</p>