

SERIES 927-072 Contacts, Tools, and Accessories

Crimp tools



MANUAL AND PNEUMATIC CRIMP TOOLS



Manual Crimp Tool

Contact Size	Wire Size	Manual Crimp Tool			Pneumatic Crimp Tool		
		Manual Tool	Turret	Universal Locator	Type A		
					Pneumatic Tool	Turret	Universal Locator
16s	16	M.105007	M.105009*	M.105012**	M.105002	M.105009*	M.105012**
16	16	M.105007	M.105009*	M.105012**	M.105002	M.105009*	M.105012**
12	12	M.105007	M.105009*	M.105012**	M.105002	M.105009*	M.105012**
8	8	/	/	/	/	/	/
4	4	/	/	/	/	/	/
0	0	/	/	/	/	/	/

* Socket contact only
** Pin contact only



Turret




Universal Locator



Pneumatic Crimp Tool Type A



Turret for Pneumatic Crimp Tool Type A



Contact Size	Wire Size	Manual Crimp Tool		
		Manual Tool	Universal Locator	Setting dimension [mm]
16s	16	M.105007	M.105012	67.7
16	16	M.105007	M.105012	73.0
12	12	M.105007	M.105012	85.4

Crimp tools for large contacts Contact insertion and removal tools

HYDRAULIC AND PNEUMATIC CRIMP TOOLS



Hydraulic Crimp Tool

Contact Size	Wire Size	Hydraulic Crimp Tool		Pneumatic Crimp Tool			
		Hydraulic Tool	Die	Type B			
				Pneumatic Tool	Die	Locator Pin	Locator Socket
16s	16	/	/	/	/	/	/
16	16	/	/	/	/	/	/
12	12	/	/	/	/	/	/
8	8	M.112004	M.112005	M.112000	M.112001	M.112308	M.112309
4	4	M.112004	M.112006	M.112000	M.112002	M.112307	M.112311
0	0	M.112004	M.112010	M.112000	M.112003	M.112306	M.112313

* Socket contact only ** Pin contact only



Die for Oleodinamic Crimp Tool



Pneumatic Crimp Tool Type B




Die For Pneumatic Crimp Tool Type B



Locator for Pneumatic Crimp Tool Type B

INSERTION AND REMOVAL TOOLS



A

Contact Size	Insertion Tool	Figure	Removal Tool	Figure
16S	M.117083	A	M.118250	C
16	M.117083	A	M.118250	C
12	M.117082	A	M.118250	C
8	M.117344	B	M.118260	D
4	M.117347	B	M.118270	D
0	M.117348	B	M.118280	D



B



C



D