

# Disposizione contatti

## Contact arrangement



Disposiz. Arrang.	Cl. isol. Rating	n° cont.	Dimens. Contatti / Contact size							
			4/0	0	4	8	12	16	18	20
10SL - 3	A	3						3		
- 4	A	2						2		
12S - 3	A	2						2		
12 - 5	A	1					1			
14S - 1	A	3						3		
- 2	I	4						4		
- 4	D	1						1		
- 5	I	5						5		
- 6	I	6						6		
- 7	A	3						3		
- 9	A	2						2		
- 07	I	7						7		
16S - 1	A	7						7		
- 3	B	1						1		
- 4	D	2						2		
- 5	A	3						3		
- 6	A	3						3		
- 8	A	5						5		
16 - 2	E	1					1			
- 7	A	3				1		2		
- 9	A	4					2	2		
- 10	A	3					3			
- 11	A	2					2			
- 12	A	1			1					
- A10	I	10							10	
18 - 1	I	10						10		
- 3	D	2					2			
- 4	D	4						4		
- 5	D	3					2	1		
- 6	D	1			1					
- 06	A	6					4	2		
- 7	B	1				1				
- 8	A	8					1	7		
- 9	I	7					2	5		
- 10	A	4					4			
- 11	A	5					5			
- 12	A	6						6		
- 13	A	4				1	3			
- 14	A	2			1			1		
- 16	C	1					1			
- 19	A	10						10		
- 20	A	5						5		
- 22	D	3						3		
- 29	A	5						5		
20 - 2	D	1		1						
- 3	D	3					3			
- 4	D	4					4			
- 6	D	3						3		
- 7	A	8						8		
- 8	I	6				2		4		
- 9	A	8					1	7		
- 11	I	13						13		
- 12	A	2			1			1		
- 14	A	5				2	3			
- 15	A	7					7			
- 16	A	9					2	7		
- 17	A	6					5	1		
- 18	A	9					3	6		
- 19	A	3				3				
- 20	A	4			1		3			
- 21	A	9					1	8		
- 22	A	6				3		3		
- 23	A	2				2				
- 24	A	4				2		2		

Disposiz. Arrang.	Cl. isol. Rating	n° cont.	Dimens. Contatti / Contact size							
			4/0	0	4	8	12	16	18	20
20 - 27	A	14							14	
- 29	A	17							17	
- 33	A	11							11	
- A9	I	9						9		
- A48	I	19							19	
- B8	A	8						4	4	
22 - 1	D	2						2		
- 2	D	3						3		
- 4	A	4						2	2	
- 5	D	6						2	4	
- 6	D	3						2	1	
- 7	E	1			1					
- 8	E	2						2		
- 9	E	3						3		
- 10	E	4							4	
- 11	B	2							2	
- 12	D	5					2		3	
- 13	D	5						4	1	
- 14	A	19							19	
- 15	A	6						5	1	
- 16	A	9						3	6	
- 17	A	9						1	8	
- 18	A	8							8	
- 19	A	14							14	
- 20	A	9							9	
- 21	A	3			1				2	
- 22	A	4					4			
- 23	A	8						8		
- 24	A	6						2	4	
- 27	A	9						1	8	
- 28	A	7							7	
- 33	A	7							7	
- 34	D	5						3	2	
- 82	A	10						2	8	
- A10	A	10							10	
- A37	A	37								37
24 - 2	D	7						7		
- 3	A	7						2	5	
- 4	A	4				1			3	
- 5	A	16							16	
- 06	D	6						4	2	
- 6	A	8							8	
- 07	D	7							7	
- 7	A	16						2	14	
- 9	A	2				2				
- 10	A	7						7		
- 11	A	9						3	6	
- 12	A	5					2		3	
- 013	A	13							6	7
- 16	A	7						1	3	3
- 17	D	5							2	3
- 19	A	12								12
- 20	D	11							2	9
- 21	D	10						1		9
- 22	D	4						4		
- 27	E	7								7
- 28	I	24								24
- 67	A	19							19	
- A1	B	1				1				
- A25	A	25								25
- A28	I	28								28
- A55	I	55								55
- G5	A	5							5	

