


## IT 3420-XX (Class A) and IT 3420-XXA (Class C) Neoprene Sleeve for Protection & Reduction used with Class A or C Cable Clamps


**IT 3420-XX**

MIL-DTL-5015 Compatible  
Accessory

Basic Part Number  
and Shell Size Designator  
(See Table I and Table II)



IT3420-XX Neoprene Sleeve used with Class A Cable Clamps



IT3420-XXA Neoprene Sleeve used with Class C Cable Clamps

D

### Application Notes:

1. IT3420-XX: Neoprene bushing for protection and reduction, used with class A cable clamps.
2. IT3420-XXA: Neoprene bushing for protection and reduction, used with class C cable clamps.
3. A broad range of other front and rear connector accessories are available.

See our website and/or contact the factory for complete information.

**IT 3420-XX (Class A) and IT 3420-XXA (Class C)  
Neoprene Sleeve for Protection & Reduction  
used with Class A or C Cable Clamps**



**TABLE I: IT3420-XX NEOPRENE SLEEVE PART NUMBERS & DIMENSIONS**

Part Number	∅A ±0.1	∅B ±0.1	∅C ±0.1	L ±0.1
IT 3420 - 4	12.8	7.67	5.58	69.8
IT 3420 - 6	15.7	10.84	7.92	66.8
IT 3420 - 8	18.8	14.02	11.09	63.5
IT 3420 - 10	22.0	15.62	14.27	60.3
IT 3420 - 12	27.0	18.79	15.87	57.1
IT 3420 - 16	33.3	23.54	19.05	53.9
IT 3420 - 20	40.5	31.49	23.79	50.8
IT 3420 - 24	46.9	34.67	31.75	47.6
IT 3420 - 28	52.9	40.99	34.92	44.4

**TABLE II: IT3420-XXA NEOPRENE PART NUMBERS & SLEEVE DIMENSIONS**

Part Number	∅A ±0.1	∅B ±0.1	L ±0.1
IT 3420 - 4A	7.63	5.56	50.5
IT 3420 - 6A	10.50	7.93	50.5
IT 3420 - 8A	13.50	11.10	50.5
IT 3420 - 10A	15.70	11.10	50.5
IT 3420 - 12A	18.50	13.74	50.9
IT 3420 - 16A	23.60	19.00	50.9
IT 3420 - 20A	31.10	23.80	50.2
IT 3420 - 24A	33.90	28.50	51.1
IT 3420 - 28A	40.60	31.80	50.2
IT 3420 - 29A	45.00	41.00	50.5