

SERIES 79 MICRO-CRIMP RECTANGULAR CONNECTORS

Backshells and Accessories

SERIES
79

799-013

Dust Cap, Anti-Static, Series 790

BACKSHELLS AND ACCESSORIES



799-013


This accessory fits Series 790 connectors.

Permanently anti-static. Non-sloughing.
Molded dust caps protect Series 790 connectors from contamination and static discharge.

- Black LDPE Material
- Static Decay per MIL-PRF-81705
- Surface Resistivity: 1E10 to 9.9E11 Ohm/SQ
- Static Decay: <2 sec @ 5kV to 50V, 12% RH

PART NUMBER								
Shell Size	Type	Part No.	A Max		C Max		D Max	
			in	mm	in	mm	in	mm
A	Plug	799-013AP	.540	13.7	.436	11.1	.320	8.1
	Recep	799-013AR	.587	14.9	.477	12.1	.320	8.1
B	Plug	799-013BP	.690	17.5	.436	11.1	.320	8.1
	Recep	799-013BR	.737	18.7	.477	12.1	.320	8.1
C	Plug	799-013CP	.840	21.3	.436	11.1	.320	8.1
	Recep	799-013CR	.887	22.5	.477	12.1	.320	8.1
D	Plug	799-013DP	.940	23.9	.436	11.1	.320	8.1
	Recep	799-013DR	.987	25.1	.477	12.1	.320	8.1
E	Plug	799-013EP	1.090	27.7	.436	11.1	.320	8.1
	Recep	799-013ER	1.137	28.9	.477	12.1	.320	8.1
F	Plug	799-013FP	1.239	31.5	.436	11.1	.320	8.1
	Recep	799-013FR	1.287	32.7	.477	12.1	.320	8.1
G	Plug	799-013GP	1.213	30.8	.529	13.4	.320	8.1
	Recep	799-013GR	1.260	32.0	.560	14.2	.320	8.1
H	Plug	799-013HP	1.586	40.3	.552	14.0	.320	8.1
	Recep	799-013HR	1.631	41.4	.587	14.9	.320	8.1
J	Plug	799-013JP	1.595	40.5	.436	11.1	.320	8.1
	Recep	799-013JR	1.642	41.7	.477	12.1	.320	8.1
K	Plug	799-013KP	1.998	50.7	.436	11.1	.320	8.1
	Recep	799-013KR	2.045	51.9	.477	12.1	.320	8.1
L	Plug	799-013LP	1.823	46.3	.552	14.0	.320	8.1
	Recep	799-013LR	1.867	47.4	.587	14.9	.320	8.1
M	Plug	799-013MP	1.878	47.7	.612	15.5	.320	8.1
	Recep	799-013MR	1.931	49.0	.647	16.4	.320	8.1
N	Plug	799-013NP	2.265	57.5	.685	17.4	.280	7.1
	Recep	799-013NR	2.335	59.3	.765	19.4	.290	7.4

SHELL SIZE A-G, J, K



SHELL SIZE H, L, M, N

