

ADVANCED -
PERFORMANCE
MIL - AERO
CONNECTOR
GO - BETWEENS




Connector Savers and
Bulkhead Feed-Thrus




Glenair Sav-Con's protected the
umbilical connectors on every
Space Shuttle mission

The smart solution for preventing contact
damage and extending the service life of
cable assemblies and box and panel-mount
receptacles



Series changers and gender changers
available in both Sav-Con® and bulkhead
feed-thru configurations



circular and rectangular configurations
available including hermetic and EMI/RFI
filter configurations

- Sav-Con®s for every mil-standard circular and rectangular connector
- Hundreds of successful space launch and space flight applications including every Space Shuttle mission
- Bulkhead feed-thrus for environmental, filter and hermetic applications
- Pin/pin, pin/socket, and socket/socket versions
- Traditional plug-receptacle savers, as well as in-line versions and gender changers
- Available EMI/EMP filter savers and adapters

HIGH-PERFORMANCE CONNECTOR GO-BETWEENS

Sav-Con® Connector Savers and Bulkhead Feed-Thrus




Each Glenair Sav-Con® Connector Saver meets the military specification performance requirements of its mating connector. Glenair manufactures and supplies a Sav-Con® connector saver for every military standard connector currently in use including:

- MIL-DTL-26482 Series I and II
- MIL-DTL-28840
- MIL-DTL-38999 Series I, II and III
- MIL-DTL-83723
- LN 29729 (SJT)
- PATT 105 and PATT 602
- MIL-DTL-5015
- Series 801 and 805 Mighty Mouse
- Series 89 Nanominiature
- M24308 D-Subminiature
- MIL-DTL-83513 Micro-D Subminiature
- Series 28 HiPer-D M24308 intermateable
- Series 79 Micro-Crimp

Comprehensive materials, plating, and polarization options available

TRADITIONAL PLUG-RECEPTACLE SAV-CON® CONNECTOR SAVERS



MIL-DTL-38999 series III type



MIL-DTL-5015 threaded and/or reverse-bayonet




MIL-DTL-38999 series II bayonet-coupling saver



Series 80 Mighty Mouse Sav-Con®

BULKHEAD FEED-THRUS



Special high-voltage power bulkhead feed-thru



Special wide panel accommodation Mighty Mouse bulkhead feed-thru




MIL-DTL-5015 bulkhead feed-thru




Special non-cadmium plating classes

SPECIAL-PURPOSE ADAPTERS AND SAVERS



EMI/RFI filter Sav-Con® adapter (D38999 Series III type shown)



Rectangular EMI/RFI filter Sav-Con adapter (MIL-DTL-83513 type shown)



Power distribution connector savers (MIL-D-5015 type shown)

