Ordering Information: El Ochito® White Contacts, Type II



El Ochito® Contacts: How To Order

Data Protocol: Cat 6A up to 10G, Cat 8 up to 40G Ethernet
El Ochito® White

Connector Type	Protocol	Wire Size	Cable Type	Recommended Cable		El Ochito® Type II	
				Glenair Part No.	Cable Dia.	Pin Contact Assembly Instr.	Skt Contact Assembly Instr.
• EN3545 Type II Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-061-01 AI85193-01P	858-062-01 AI85193-01S
	Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-061-02 AI85193-02P	858-062-02 AI85193-02S
	Cat 6A	24	S/UTP	963-037-24	.260 (6.60)	858-061-03 AI85193-03P	858-062-03 AI85193-03S
	Cat 6A	24	S/FTP	963-033-24	.260 (6.60)	858-061-04 AI85193-04P	858-062-04 AI85193-04S
	Cat 6A	24	S/UTP	963-003-24	.280 (7.11)	858-061-05 AI85193-05P	858-062-05 AI85193-05S
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-061-06 AI85193-06P	858-062-06 AI85193-06S
	Cat 8	24	S/FTP	963-132-24	.260 (6.60)	858-061-07 AI85193-07P	858-062-07 AI85193-07S
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-061-08 AI85193-08P	858-062-08 AI85193-08S
• SuperNine® (Series 23) • HiPer-D® (Series 28) Type II Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-005-01 AI85097-01	858-006-01 AI85097-01
	Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-005-02 AI85097-02	858-006-02 AI85097-02
	Cat 6A	24	S/UTP	963-037-24	.260 (6.60)	858-005-03 AI85097-03	858-006-03 AI85097-03
	Cat 6A	24	S/FTP	963-033-24	.260 (6.60)	858-005-04 AI85097-04	858-006-04 AI85097-04
	Cat 6A	24	S/UTP	963-003-24	.280 (7.11)	858-005-05 AI85097-05	858-006-05 AI85097-05
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-005-06 AI85097-06	858-006-06 AI85097-06
	Cat 8	24	S/FTP	963-132-24	.260 (6.60)	858-005-07 AI85097-07	858-006-07 AI85097-07
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-005-08 AI85097-08	858-006-08 AI85097-08

© 2022 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324 • El Ochito® Octaxial Contacts
Dimensions in Inches (millimeters) are subject to change without notice.

Ordering Information: El Ochito® White Contacts, Type II

El Ochito® Contacts: How To Order

Data Protocol: Cat 6A up to 10G, Cat 8 up to 40G Ethernet
El Ochito® White

Connector Type	Protocol	Wire Size	Cable Type	Recommended Cable		El Ochito® Type II	
				Glenair Part No.	Cable Dia.	Pin Contact Assembly Instr.	Skt Contact Assembly Instr.
• Series 792 Type II Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-043-01 AI85134-01	858-042-01 AI85134-02
	Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-043-02 AI85134-02	858-042-02 AI85134-02
	Cat 6A	24	S/UTP	963-037-24	.260 (6.60)	858-043-03 AI85134-02	858-042-03 AI85134-02
	Cat 6A	24	S/FTP	963-033-24	.260 (6.60)	858-043-04 AI85134-04	858-042-04 AI85134-04
	Cat 6A	24	S/UTP	963-003-24	.280 (7.11)	858-043-05 AI85134-05	858-042-05 AI85134-05
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-043-06 AI85134-06	858-042-06 AI85134-06
	Cat 8	24	S/FTP	963-132-24	.260 (6.60)	858-043-07 AI85134-07	858-042-07 AI85134-07
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-043-08 AI85134-08	858-042-08 AI85134-08
• Series 806 • Series 816 Type II Contacts	Cat 6A	26	S/UTP	963-003-26	.220 (5.59)	858-051-01 AI85149-01	858-052-01 AI85149-02
	Cat 6A	26	S/FTP	963-033-26	.220 (5.59)	858-051-02 AI85149-02	858-052-02 AI85149-02
	Cat 6A	24	S/UTP	963-037-24	.260 (6.60)	858-051-03 AI85149-03	858-052-03 AI85149-03
	Cat 6A	24	S/FTP	963-033-24	.260 (6.60)	858-051-04 AI85149-04	858-052-04 AI85149-04
	Cat 6A	24	S/UTP	963-003-24	.280 (7.11)	858-051-05 AI85149-05	858-052-05 AI85149-05
	Cat 8	26	S/FTP	963-132-26	.220 (5.59)	858-051-06 AI85149-06	858-052-06 AI85149-06
	Cat 8	24	S/FTP	963-132-24	.260 (6.60)	858-051-07 AI85149-07	858-052-07 AI85149-07
	Cat 8	26	S/FTP	963-135-26	.220 (5.59)	858-051-08 AI85149-08	858-052-08 AI85149-08

© 2022 Glenair, Inc • 1211 Air Way, Glendale, CA 91201 • 818-247-6000 • www.glenair.com • U.S. CAGE code 06324 • El Ochito® Octaxial Contacts

Dimensions in Inches (millimeters) are subject to change without notice.