

MICRO-CRIMP RECTANGULAR CONNECTORS

Series 792 High-Speed



792-010

PCB Receptacle, 90° Tails, El Ochito®

- ◆ Octaxial PC tail contacts
- ◆ 90° mounting
- ◆ Pin contacts

OCHITO PROTOCOLS



WHITE
1000BASE-T
10GBASE-T



BLUE
USB 3.0



RED
HDMI, SATA,
DisplayPort

The Ochito octaxial contact is color-coded to signify the data protocol. White is used for high speed Ethernet, blue is used for USB 3.0, and red is used for multi gigabit 100 ohm protocols including HDMI, DisplayPort and SATA. The connector part number includes a code from the **Protocol Code** table. This code enables combinations of protocols as shown in the examples below.




Code AA



Code AH


PROTOCOL CODE

Code	Cavity				
	A1	A2	A3	A4	A5
AA	W	W	W	W	W
AB	B	W	W	W	W
AC	R	W	W	W	W
AD	B	B	W	W	W
AE	R	B	W	W	W
AF	R	R	W	W	W
AG	B	B	B	W	W
AH	R	B	B	W	W
AJ	R	R	B	W	W
AK	R	R	R	W	W
AL	B	B	B	B	W
AM	R	B	B	B	W
AN	R	R	B	B	W
AP	R	R	R	B	W
AQ	R	R	R	R	W
AR	B	B	B	B	B
AS	R	B	B	B	B
AT	R	R	B	B	B
AV	R	R	R	B	B
AW	R	R	R	R	B
AX	R	R	R	R	R



Shell Size	A Max		B ± .005 (0.1)		C Max		D ± .005 (0.1)		E ± .002 (0.05)	
	in	mm	in	mm	in	mm	in	mm	in	mm
A	1.455	36.96	1.075	27.31	.690	17.53	1.075	27.31	.725	18.42
B	1.830	46.48	1.450	36.83	1.065	27.05	1.450	36.83	1.100	27.94
C	2.205	56.01	1.825	46.36	1.440	36.58	1.825	46.36	1.475	37.47
D	2.580	65.53	2.200	55.88	1.815	46.10	2.200	55.88	1.850	46.99
E	2.955	75.06	2.575	65.41	2.190	55.63	2.575	65.41	2.225	56.52

PANEL CUTOUT



MICRO-CRIMP RECTANGULAR CONNECTORS

Series 792 High-Speed



792-010

PCB Receptacle, 90° Tails, El Ochito®

- ◆ Octaxial PC tail contacts
- ◆ 90° mounting
- ◆ Pin contacts



PCB FOOTPRINTS FOR 792-010 CONNECTOR

⚠ Optimizing PCB Design


See Glenair Application Note AN0002 *Design and Installation of El Ochito PCB Connectors* for recommended solder pad sizing, trace routing, and connector installation.
<https://cdn.glenair.com/test-reports-and-technical-information/pdf/application-note/an0002.pdf>

⚠ PCB hole patterns are shown for the **component mounting side** of the circuit board, looking through the connector.


Detail B




A-1P1 A-1G1




A-3P1




B-2P2 B-2G2




B-6P2




B-23P1



C-3P3 C-3G3



C-9P3



C-24P2

Glenair®

PCB Receptacle, 90° Tails, El Ochito®

- ◆ Octaxial PC tail contacts
- ◆ 90° mounting
- ◆ Socket contacts

SERIES 792 HIGH-SPEED

