




Glenair IPT SE Series Insert Arrangement Tables and Sealing Plugs

Sealing Plugs for Socket Cavity




SEALING PLUG DIMENSIONS

Part Number	D1 ±0.1	D2 ±0.2	L1 ±0.1	L2 ±0.3	Color
DIN 65194-20	1.62	2.3	3.5	14.5	Red
DIN 65194-16	2.30	3.4	3.1	14.5	Blue


Insert Arrangement Tables

Arrangement	Cl. Isol. Rating	Dim. contact size	
		20	16
8 - 2	I	2	
8 - 3A	I	3	
8 - 4	I	4	
8-33	I	3	
10 - 6	I	6	
10 - 7	I	7	
12 - 3	II		3
12 - 10	I	10	
14 - 5	II		5
14 - 12	I	8	4
14 - 15	I	14	1
14 - 19	I	19	
16 - 8	II		8
16 - 23	I	22	1
16 - 26	I	26	
18 - 11	II		11
18 - 32	I	32	
20 - 16	II		16
20 - 39	I	37	2
20 - 41	I	41	
22 - 21	II		21
22 - 55	I	55	
24 - 61	I	61	


Arrangement	Degrees			
	W	X	Y	Z
8 - 2	58	122		
8 - 3A	60			
8 - 4	45			
8-33	90			
10 - 6	90			
10 - 7	90			
12 - 3			180	
12 - 10	60	155	270	295
14 - 5	40	92	184	273
14 - 12	43	90		
14 - 15	17	110	155	234
14 - 19	30	165	315	
16 - 8	54	152	180	331
16 - 23	158			
16 - 26	60		275	338
18 - 11	62	119	241	340
18 - 32	85	138	222	265
20 - 16	238	318	333	347
20 - 39	63	144	252	333
20 - 41	45	126	225	
22 - 21	16	135	175	349
22 - 55	30	142	226	314
24 - 61	90	180	270	324



Normal
Position



Alternate Position
with Pin Contacts



Alternate Position
with Socket Contacts

Glenair IPT SE Series Available Insert Arrangements



2 Contacts



Arrangement:	8-2
Contact Size:	20
Service Rating:	I

4 Contacts




Arrangement:	8-4
Contact Size:	20
Service Rating:	I

6 Contacts




Arrangement:	10-6
Contact Size:	20
Service Rating:	I

8 Contacts




Arrangement:	16-8
Contact Size:	16
Service Rating:	II

11 Contacts




Arrangement:	18-11
Contact Size:	16
Service Rating:	II

15 Contacts



Arrangement:	14-15
Contact Size:	14-20, 1-16
Service Rating:	I

3 Contacts




Arrangement:	8-3A	8-33	12-3
Contact Size:	20	20	16
Service Rating:	I	I	II

5 Contacts



Arrangement:	14-5
Contact Size:	16
Service Rating:	II

7 Contacts




Arrangement:	10-7
Contact Size:	20
Service Rating:	I

10 Contacts




Arrangement:	12-10
Contact Size:	20
Service Rating:	I

12 Contacts



Arrangement:	14-12
Contact Size:	8-20, 4-16
Service Rating:	I

16 Contacts



Arrangement:	20-16
Contact Size:	16
Service Rating:	II


Contact
Legend



Glenair IPT SE Series


Available Insert Arrangements

19 Contacts




Arrangement:	14-19
Contact Size:	20
Service Rating:	I

23 Contacts




Arrangement:	16-23
Contact Size:	22-20, 1-16
Service Rating:	I

32 Contacts




Arrangement:	18-32
Contact Size:	20
Service Rating:	I

41 Contacts




Arrangement:	20-41
Contact Size:	20
Service Rating:	I

61 Contacts




Arrangement:	24-61
Contact Size:	20
Service Rating:	I

21 Contacts




Arrangement:	22-21
Contact Size:	16
Service Rating:	II

26 Contacts




Arrangement:	16-26
Contact Size:	20
Service Rating:	I

39 Contacts



Arrangement:	20-39
Contact Size:	37-20, 2-16
Service Rating:	I

55 Contacts



Arrangement:	22-55
Contact Size:	20
Service Rating:	I

Contact
Legend

