AS85049/37 and M38999/8
90° EMI/RFI Non-Environmental Backshell

CONNECTOR DESIGNATOR:	
F	MIL-DTL-38999 Series I and II

Finish

N = Electroless Nickel
W = 1,000 Hr. Cadmium Olive Drab over Electroless Nickel
X = Nickel Fluorocarbon Polymer
Z = Zinc-Nickel, Black

M85049/37	10	W	03	L
Basic Part Number	Shell Size (Table I)		Clamp Size (Table I)	D = 3 Drain Holes L = Encapsulating Hole

TABLE I: Shell Size

Shell Size Series II	Series I Shell Size Ref.	A Thread Class 2B	C Dia Max
08	09	.438 - 28 UNEF	.750 (19.1)
10	11	.562 - 24 UNEF	.850 (21.6)
12	13	.688 - 24 UNEF	1.000 (25.4)
14	15	.813 - 20 UNEF	1.100 (27.9)
16	17	.938 - 20 UNEF	1.250 (31.8)
18	19	1.063 - 18 UNEF	1.400 (35.6)
20	21	1.188 - 18 UNEF	1.500 (38.1)
22	23	1.313 - 18 UNEF	1.650 (41.9)
24	25	1.438 - 18 UNEF	1.750 (44.5)



TABLE II: Clamp Size and Dimensions

Shell Size Series II	Series I Shell Size Ref.	E Max	F Max	Clamp Size Min	Clamp Size Max
8	09	.720 (18.3)	2.88 (73.15)	01	02
10	11	.720 (18.3)	2.92 (74.17)	01	03
12	13	.800 (20.3)	3.06 (77.72)	02	04
14	15	.850 (21.6)	3.24 (82.30)	02	05
16	17	.910 (23.1)	3.44 (87.38)	02	06
18	19	1.000 (25.4)	3.73 (94.74)	03	06
20	21	1.050 (26.7)	3.94 (100.08)	03	07
22	23	1.100 (27.9)	4.14 (105.16)	03	08
24	25	1.200 (30.5)	4.19 (106.43)	04	09

TABLE II: Clamp Size and Dimensions

Clamp Size	Cable Range Min	Cable Range Max	G Max
01	.062 (1.6)	.125 (3.2)	.781 (19.8)
02	.125 (3.2)	.250 (6.4)	.969 (24.6)
03	.250 (6.4)	.375 (9.5)	1.062 (27.0)
04	.312 (7.9)	.500 (12.7)	1.156 (29.4)
05	.437 (11.1)	.625 (15.9)	1.250 (31.8)
06	.562 (14.3)	.750 (19.1)	1.375 (34.9)
07	.687 (17.4)	.875 (22.2)	1.500 (38.1)
08	.812 (20.6)	1.000 (25.4)	1.625 (41.3)
09	.937 (23.8)	1.125 (28.6)	1.750 (44.5)

APPLICATION NOTES

1. For complete dimensions see the applicable Military Specification.
2. Metric dimensions (mm) are in parentheses.
3. Cable Range is defined as the accommodation range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.

Dimensions in inches (millimeters) and are subject to change without notice.

© 2013 Glenair, Inc. Mil-Spec Backshells U.S. CAGE Code 06324 Rev. 05.29.15 Printed in U.S.A.