

CONNECTOR CONTACTS IT - ITS - ITS-RG - ITZ Connectors




Socket Crimp Contacts - Manual and Pneumatic Tools

A

Manual and Pneumatic Tools Table							
Part Number	Contact Size	Wire Size		Manual Crimp Tool		Pneumatic Tool Type "A"	
		mm ²	AWG	Manual Tool	Turret	Pneumatic Tool	Turret
10-40520LC	20	0,15-0,6	26-20	M.105001	M.105026	M.105003	M.105026
10-40588	18	0,15-0,6	26-20	M.105001	M.105025	M.105003	M.105025
10-40552	16S	1-1,5	18-16	M.105007	M.105009	M.105002	M.105009
10-40552-12	16S	0,6	20	M.105007	M.105009	M.105002	M.105009
10-40552-13	16S	0,15-0,6	26-20	M.105001	M.105009	M.105003	M.105009
10-40552-15	16S	0,75-1	18	M.105007	M.105009	M.105002	M.105009
10-40552-20	16S	1-2	14	M.105007	M.105009	M.105002	M.105009
10-40552-26	16S	2,5-3,0	12	M.105007	M.105009	M.105002	M.105009
10-40556	16	1-1,5	18-16	M.105007	M.105009	M.105002	M.105009
10-40556-08	16	0,15-0,2	26-24	M.105001	M.105009	M.105003	M.105009
10-40556-12	16	0,6	20	M.105007	M.105009	M.105003	M.105009
10-40556-13	16	0,15-0,6	26-20	M.105001	M.105009	M.105003	M.105009
10-40556-15	16	0,75-1	18	M.105007	M.105009	M.105002	M.105009
10-40556-20	16	1-2	14	M.105007	M.105009	M.105002	M.105009
10-40556-22	16	2,5	/	M.105007	M.105009	M.105002	M.105009
10-40556-26	16	2,5-3,0	12	M.105007	M.105009	M.105002	M.105009
10-40556-32	16	/	32-28	M.105007	M.105009	M.105003	M.105009
10-40560	12	2,5-3,0	12	M.105007	M.105009	M.105002	M.105009
10-40560-12	12	0,6	20	M.105007	M.105009	M.105003	M.105009
10-40560-15	12	0,75-1	18	M.105007	M.105009	M.105002	M.105009
10-40560-177	12	1,5	18-16	M.105007	M.105009	M.105002	M.105009
10-40560-20	12	2	14	M.105007	M.105009	M.105002	M.105009
10-40560-22	12	2,5	/	M.105007	M.105009	M.105002	M.105009
10-40560-30	12	4-5	/	M.105007	M.105009	M.105002	M.105009
10-40560-30M	12	4	/	M.105007	M.105009	M.105002	M.105009
10-40560-38	12	6	10	M.105007	M.105009	M.105002	M.105009

Please consult our sales department for other contact options or crimp tooling details.



CONNECTOR CONTACTS IT - ITS - ITS-RG - ITZ Connectors



Socket Crimp Contacts - Manual and Pneumatic Tools

A

Manual and Pneumatic Tools Table										
Part Number	Contact Size	Wire Size		Manual Crimp Tool		Pneumatic Tool Type "B"			Oleodynamic Tool	
		mm ²	AWG	Manual Tool	Turret	Pneumatic Tool	Die	Locator	Oleodynamic Tool	Die
10-40793-1	8	9	8	/	/	M.112000	M.112001	M.112309	M.112004	M.112005
10-40793-1-15	8	0,75-1	18	M.105028	M.104002	/	/	/	/	/
10-40793-1-18	8	1-2	18-14	M.105028	M.104002	/	/	/	/	/
10-40793-1-20	8	2	14	M.105028	M.104002	/	/	/	/	/
10-40793-1-26	8	3	12	M.105028	M.104002	/	/	/	/	/
10-40793-1-30	8	4-5	/	M.105028	M.104002	/	/	/	M.112004	M.112008
10-40793-1-38	8	6	10	/	/	M.112000	M.112001	M.112309	M.112004	M.112005
10-40793-1-50	8	10	/	/	/	M.112000	M.112001	M.112309	M.112004	M.112005
10-10793-1-58	8	13,2	6	/	/	M.112000	M.112001	M.112309	M.112004	M.112005
10-113474-4S-1	4	25	4	/	/	M.112000	M.112002	M.112311	M.112004	M.112006
10-113474-4S-1-22	4	2,5	/	/	/	/	/	/	M.112004	M.112009
10-113474-4S-1-26	4	3	/	/	/	/	/	/	M.112004	M.112009
10-113474-4S-1-30	4	4-5	/	/	/	/	/	/	M.112004	M.112008
10-113474-4S-1-38	4	6	10	/	/	M.112000	M.112001	M.112311	M.112004	M.112005
10-113474-4S-1-50	4	10	/	/	/	M.112000	M.112001	M.112311	M.112004	M.112005
10-113474-4S-1-58	4	13,2	6	/	/	M.112000	M.112001	M.112311	M.112004	M.112005
10-113474-4S-62	4	16	/	/	/	M.112000	M.112002	M.112311	M.112004	M.112006
10-113474-1S	0	50-60	0	/	/	M.112000	M.112003	M.112313	M.112004	M.112010
10-113474-1S-107	0	50	/	/	/	M.112000	M.112003	M.112313	M.112004	M.112010
10-113474-1S-72	0	22-25	4	/	/	M.112000	M.112002	M.112313	M.112004	M.112006
10-113474-1S-35	0	35	/	/	/	/	/	/	M.112004	M.112007
10-113474-1S-45	0	9	8	/	/				M.112004	M.112005
10-113474-1S-50	0	10	/	/	/				M.112004	M.112005
10-113474-1S-58	0	13,2	6	/	/				M.112004	M.112005
10-113474-1S-62	0	16	/	/	/				M.112004	M.112006
10-113474-0S	4/0	107	4/0	/	/	/	/	/	M.105013	M.112012
10-113474-0S-78	4/0	25	/	/	/	/	/	/	M.112004	M.112006
10-113474-0S-107	4/0	50	/	/	/	/	/	/	M.112004	M.112010
10-113474-0S-144	4/0	70	/	/	/	/	/	/	M.105013	M.105053

Please consult our sales department for other contact options or crimp tooling details.

Manual and Pneumatic Tools				
				
Pneumatic Crimp Tool Type "B"	Die For Pneumatic Crimp Tool Type "B"	Locator for Pneumatic Crimp Tool Type "B"	Oleodynamic Crimp Tool	Die for Oleodynamic Crimp Tool