

Series 31 Shrink Boot Adapters

for MIL-DTL-38999 Series I and II Connectors

310FS034 Shrink Boot Adapter, Direct Coupling



Adapter Code F

This accessory fits these connectors:
MIL-DTL-38999 Series I and Series II

SHRINK BOOT

Optional heatshrink boot provides cable strain relief and environmental protection. Type 1 high-performance semi-rigid elastomer resists fuels and oils and withstands temperature extremes.




Shell Size	Shrink Boot P/N
08	770-001S103
10	770-001S103
12	770-001S104
14	770-001S106
16	770-001S106
18	770-001S107
20	770-001S107
22	770-001S108
24	770-001S108

Direct coupling. Low profile. 310FS034 shrink boot adapter fits MIL-DTL-38999 Series I and II connectors. Adapter has groove for lipped shrink boot. Supplied as adapter only or as kit with shrink boot. Aluminum or stainless steel, silicone O-ring.

PART NUMBER

310FS034 NF 14 T

Base P/N	310FS034										
Material/Finish	M	Alum/ Electroless Nickel									
	MT	Alum/ Nickel-PTFE									
	NF	Alum/ Olive Drab Cadmium									
	ZR	Alum/ Black Zinc-Nickel									
	TZ	Alum/ Tin-Zinc									
	ZI	SST/ Passivated									
Shell Size	Shell Size										
	38999 Series I	9	11	13	15	17	19	21	23	25	
	38999 Series II	8	10	12	14	16	18	20	22	24	
	Size Code	08	10	12	14	16	18	20	22	24	
Shrink Boot	<i>Omit if not required</i>										
	T	Shrink Boot included									



Shell Size	A Thread UNEF-2B	ø B Max		K Max		ø L Max		Cable Entry Min	
		in	mm	in	mm	in	mm	in	mm
8/9	0.4375-28	.59	15.0	.500	12.7	.688	17.5	.250	6.4
10/11	0.5625-24	.72	18.3	.500	12.7	.803	20.4	.355	9.0
12/13	0.6875-24	.84	21.3	.500	12.7	.938	23.8	.491	12.5
14/15	0.8125-20	.97	24.6	.500	12.7	1.063	27.0	.565	14.4
16/17	0.9375-20	1.09	27.7	.500	12.7	1.238	31.4	.690	17.5
18/19	1.0625-18	1.22	31.0	.500	12.7	1.310	33.3	.769	19.5
20/21	1.1875-18	1.34	34.0	.500	12.7	1.436	36.5	.844	21.4
22/23	1.3125-18	1.47	37.3	.500	12.7	1.560	39.6	1.019	25.9
24/25	1.4375-18	1.59	40.4	.500	12.7	1.686	42.8	1.134	28.8