

Crown Ring crimp contact tooling


PNEUMATIC CRIMP TOOL FOR #8, #4 AND #1/0 CONTACTS



C Bench mount pneumatic crimp tool. Heavy duty, four-indent crimp termination. Attach to air supply with quick-disconnect fitting or install 1/4 NPT fitting into tapped port. 90-120 psi air supply. Requires die assemblies and locators, sold separately. Hand actuate with push-button valve trigger on handle. Steel with black wrinkle enamel coating. 13 inches overall length, 9.2 inches tall, 17 pounds (7.7 Kg).

D Indenter Die Assembly. Precision four-indent die with hardened tool steel indenters, stainless steel housing. Separate die assembly required for each contact size.

E Locator. Aluminum locator positions contact at correct depth for crimping. Separate locator required for each contact size.



CROWN RING CRIMP CONTACT TOOLING							
Contact Size	Contact Part Number		Extraction Tool		Crimp Tool	Die Set	Locator
	Pin	Socket	Plastic	Metal			
8AWG	850-150-8	850-151-8	859-136-8 or M81969/29-02	859-139	859-025	859-026	859-029
4AWG	850-150-4	850-151-4	859-136-4 or M81969/29-03	859-138		859-027	859-030
2AWG	850-150-2	850-151-2	N/A	859-171		859-169	859-170
1/0AWG	850-150-0	850-151-0	M81969/14-08 or M81969/29-04	859-137		859-028	859-031