


Recommended panel cut-outs

REFERENCE INFORMATION



Series II and IV, Recommended Panel Cut-Out Dimensions											
Shell Size Code	Shell Size	A Dia	AA Dia	B* +.00 -.25	C +.25 -.00	E dia min	F +.00 -.25	G +.25 -.00	R1	R2	T dia $\pm .13$
A	8-9	.656 (16.66)	.516 (13.11)	.657 (16.69)	.693 (17.60)	.557 (14.15)	.830 (21.08)	.885 (22.48)	.719 (18.26)	.594 (15.09)	.128 (3.25)
B	10-11	.796 (20.22)	.625 (15.88)	.771 (19.58)	.825 (20.96)	.682 (17.32)	.955 (24.26)	1.010 (25.65)	.812 (20.62)	.719 (18.26)	.128 (3.25)
C	12-13	.922 (23.42)	.750 (19.05)	.955 (24.26)	1.010 (25.65)	.854 (21.69)	1.085 (27.56)	1.135 (28.83)	.906 (23.01)	.812 (20.62)	.128 (3.25)
D	14-15	1.047 (26.59)	.906 (23.01)	1.085 (27.56)	1.135 (28.83)	.979 (24.87)	1.210 (30.73)	1.260 (32.00)	.969 (24.61)	.906 (23.01)	.128 (3.25)
E	16-17	1.219 (30.96)	1.016 (25.81)	1.210 (30.73)	1.260 (32.00)	1.104 (28.04)	1.335 (33.91)	1.385 (35.18)	1.062 (26.97)	.969 (24.61)	.128 (3.25)
F	18-19	1.297 (32.94)	1.141 (28.98)	1.335 (33.91)	1.385 (35.18)	1.229 (31.22)	1.460 (37.08)	1.510 (38.35)	1.156 (29.36)	1.062 (26.97)	.128 (3.25)
G	20-21	1.422 (36.12)	1.266 (32.16)	1.460 (37.08)	1.510 (38.35)	1.354 (34.39)	1.585 (40.26)	1.635 (41.53)	1.250 (31.75)	1.156 (29.36)	.128 (3.25)
H	22-23	1.547 (39.29)	1.375 (34.92)	1.585 (40.26)	1.635 (41.53)	1.479 (37.57)	1.709 (43.41)	1.760 (44.70)	1.375 (34.92)	1.250 (31.75)	.154 (3.91)
J	24-25	1.672 (42.47)	1.484 (37.69)	1.710 (43.43)	1.760 (44.70)	1.604 (40.74)	1.835 (46.61)	1.885 (47.88)	1.500 (38.10)	1.375 (34.92)	.150 (3.81)