

SERIES ## 28840 SuperSeal™




USB and RJ45 Connector Specifications and Polarization Options

Material and Finish	
Shell, Barrel, Coupling Nut, Jam Nut	See Material and Finish Table
Insulators	High grade rigid dielectric/N.A.
Contacts	Copper alloy, gold plated
Seals	Silicone based elastomer
Coupler Housing	UL94V-0 compliant PPS
Dielectric	Hi-temp thermoplastic
Hardware	Stainless steel/passivated

Specifications		
Property	USB 2.0 Connectors	RJ12 and RJ45 Connectors
Shielding	Continuous	
Wiring	Straight Through	
Current Rating	1.5 Amp	
D.W.V.	500 VAC	1000 VDC (700 VAC)
I.R.	1000 MegOhms Minimum	500 MegOhms @ 500 VDC
Operating Temperature Range	-40° C to +120° C	-40° C to +120° C

MIL-DTL-28840 POLARIZATION KEY AND KEYWAY ARRANGEMENTS



Alternate Keyways					
Designator	Key and Keyway Arrangement	AR° or AP° BSC	BR° or BP° BSC	CR° or CP° BSC	DR° or DP° BSC
C (15) D (17)	1	80	142	196	293
	2	135	170	200	310
	3	49	169	200	244
	4	66	140	200	257
	5	62	145	180	280
	6	79	153	197	272
E (19)	1	80	142	196	293
	2	135	170	200	310
	3	49	169	200	244
	4	66	140	200	257
	5	62	145	180	280
	6	79	153	197	272