




# NEXT-GENERATION SpeedMaster™ 10G high-speed solutions Product Selection Guide



<b>SpeedMaster Contact Module</b>	
<b>Contact Module Overview</b>	page 4
<b>Contact Ordering Information</b>	
Pre-wired 10G high-speed contacts Modules	page 6
10G High-speed Pin and Socket Modules	page 8
<b>Contact Module 10G Compliance Testing</b>	page 10
<b>Contact Module Assembly Instructions</b>	page 30
<b>Installation Instructions for:</b>	
Mighty Mouse (AI85087)	page 33
HiPer-D (AI85089)	page 34
SuperNine (AI85086)	page 35



<b>Mighty Mouse</b>	
<b>Series 824 Product Specifications</b>	page 10
<b>Series 824 Connectors</b>	page 12
824-009-06 Plug	
824-010-01 In-line Receptacle	
824-010-00 Front Panel Mount, Jam Nut Receptacle	
824-010-07 Rear Panel Mount, Jam Nut Receptacle	



<b>HiPer-D (M24308)</b>	
<b>Series 28 In-Line Connectors</b>	page 14
280-101M Plug	
280-098F Receptacle	
<b>Series 28 Rear Panel Mount Connectors</b>	page 16
280-102M Plug	
280-099F Receptacle	
<b>Series 28 Float Mount Connectors</b>	page 18
280-103M Plug	
280-100F Receptacle	



<b>SuperNine (38999 type)</b>	
<b>Series 23 Specifications</b>	page 20
<b>Series 23 Connectors</b>	page 22
233-219-G6 Plug	
233-219-00 Wall Mount Receptacle	
233-219-07 Jam Nut Receptacle	
377-118 Composite Backshell	
<b>Series 23 Backshells</b>	page 28
377-119 Aluminum Alloy Backshell	