






















Selection Guide: El Ochito® Red for Multi-gig and SATA

Quick Disconnect for Multi-Gig SATA and General High Speed






	882-023 Cable Plug77 Multi-gig, 100 Ohm choose Integral band platform or cable grommet backshell. Supplied as unassembled kit. Mates with 882-024, 027, -030, -040.		882-030 90° PCB Receptacle83 Multi-gig, 100 Ohm rear panel mount, jam-nut receptacle. O-ring seals and epoxy potting for watertight sealing. Mates with 882-023, -031, -034, -037.
	882-024 Cable Receptacle78 Multi-gig, 100 Ohm choose Integral band platform or cable grommet backshell. Supplied as unassembled kit. Mates with 882-023, -031, -034, -037.		882-034 90° PCB Plug84 Multi-gig, 100 Ohm PCB 90° rear panel mount, jam-nut plug. O-ring seals and epoxy potting for watertight sealing. Mates with 882-024, -027, -030, -040.
	882-037 Panel Mount Plug79 Multi-gig, 100 Ohm integral backshell and cable grommet. Supplied as unassembled kit. Mates with 882-011, -024, -027, -030, and -040.		8573-0025 Cordset, Single-ended 85 Multi-gig, 100 ohm pre-wired single-ended, SuperFly QDC plug or receptacle, opposite end is unterminated
	882-040 Panel Mount Receptacle80 Multi-gig, 100 Ohm choose Integral band platform or cable grommet backshell. Supplied as unassembled kit. Mates with 882-023, -031, -034, -037.		8573-0026 Cordset, Double-ended 86 Multi-gig, 100 ohm cordset with SuperFly QDC plug on one end and receptacle connector on opposite end.
	882-031 PCB Plug81 Multi-gig, 100 ohm, rear panel mount, jam-nut receptacle. O-ring seals and epoxy potting for watertight sealing. Mates with 882-024, -027, -030, -040.		8573-0038 Cordset, Single-ended 87 SATA 3.0, 100 Ohm cordset with SuperFly connectors on one end, opposite end is unterminated
	882-027 PCB Receptacle82 Multi-gig, 100 Ohm PCB, rear panel mount, jam-nut receptacle. O-ring seals and epoxy potting for watertight sealing. Mates with 882-023, -031, -034, -037.		8573-0039 Cordset, Double-ended 88 SATA 3.0, 100 ohm cordset with SuperFly connectors, plug to receptacle.

Selection Guide: El Ochito® Red for Multi-gig and SATA

Threaded Coupling, Multi-Gig 100 Ohm for SATA and General High Speed

 <p>882-025 Cable Plug 89 Choose integral band porch or cable grommet backshell. Kit supplied unassembled. Mates with 882-026, -028, -029 and -043.</p>	 <p>8573-0027 Cordset, Single-ended 94 Multi-gig, pre-wired single-ended cordset with cable grommet backshell. Four aerospace-grade cable options available.</p>
 <p>882-026 Cable Receptacle 90 Choose integral band porch or cable grommet backshell. Kit supplied unassembled. Mates with 882-025.</p>	 <p>8573-0028 Cordset, Double-ended 95 Multi-gig pre-wired plug-to-receptacle cordset with cable grommet backshell. Four aerospace-grade cable options available.</p>
 <p>882-043 Panel Mount Receptacle 91 Choose integral band porch or cable grommet backshell. Kit supplied unassembled. Mates with 882-025.</p>	 <p>8573-0040 Cordset, Single-ended 96 SATA 3.0, pre-wired single-ended cordset SuperFly QDC plug or receptacle, opposite end is unterminated.</p>
 <p>882-028 PCB Receptacle 92 100 ohm, rear panel mount, jam-nut receptacle. O-ring seals and epoxy potting for watertight sealing. Mates with 882-025.</p>	 <p>8573-0041 SATA 3.0 Cordset 97 SATA 3.0 pre-wired plug-to-receptacle cordset with cable grommet backshell.</p>
 <p>882-029 90° PCB Receptacle 93 100 ohm, 90° rear panel mount, jam-nut receptacle. O-ring seals and epoxy potting for watertight sealing. Mates with 882-025.</p>	

HDMI, DP, SATA and General High Speed Cables

 <p>963-120 HDMI and DP Cable 98 Aerospace-grade 26 AWG, S/FTP construction with foil shielded data pairs. High performance cable offers three jacket material options. Meets HDMI 2.0 and DispPort 1.2 upto 5 meters.</p>	 <p>963-033-26 S/FTP High-Speed Cable 99 26 AWG, aerospace-grade S/FTP construction, foil shielded data pairs and overall 40 AWG silver plated copper braid. Meets ANSI/TIA 568-C.2 Cat 6A requirement up to 213 ft/65 m</p>
 <p>963-127 HDMI and DP Cable 98 26 AWG, S/FTP construction, foil shielded data pairs and overall 36 AWG tin/copper. Jacket available in three material options. Meets HDMI 2.0 and DisplayPort 1.2 upto 5 meters.</p>	 <p>963-133 SATA Cable 100 24 AWG, foil shielded data pairs and 38 AWG silver plated copper braid and overall blue FEP jacket.</p>
 <p>963-122 S/FTP High-Speed Cable 99 4 data pair aerospace-grade 26 AWG, S/FTP construction, foil shielded data pairs and overall 40 AWG silver plated copper braid. Three jacket material options.</p>	