

CONNECTOR CONTACTS IT - ITS - ITS-RG - ITZ Connectors




Pin Crimp Contacts - Manual and Pneumatic Tools

A

Manual and Pneumatic Tools Table							
Part Number	Contact Size	Wire Size		Manual Crimp Tool		Pneumatic Tool Type "A"	
		mm ²	AWG	Manual Tool	Turret	Pneumatic Tool	Turret
10-375-20	20	0,15-0,6	26÷20	M.105001	M.105026	M.105003	M.105026
10-40579	18	0,15÷0,6	26÷20	M.105001	M.105025	M.105003	M.105025
10-40553	16S	1÷1,5	18÷16	M.105007	M.105009	M.105002	M.105009
10-40553-12	16S	0,6	20	M.105007	M.105009	M.105002	M.105009
10-40553-13	16S	0,15÷0,6	26÷20	M.105001	M.105009	M.105003	M.105009
10-40553-15	16S	0,75-1,0	18	M.105007	M.105009	M.105002	M.105009
10-40553-20	16S	1-2	14	M.105007	M.105009	M.105002	M.105009
10-40553-26	16S	2,5-3,0	12	M.105007	M.105009	M.105002	M.105009
10-40557	16	1÷1,5	18÷16	M.105007	M.105009	M.105002	M.105012
10-40557L	16	1÷1,5	18÷16	M.105007	M.105012	M.105002	M.105009
10-40557-08	16	0,15÷0,2	26÷24	M.105001	M.105009	M.105003	M.105009
10-40557-12	16	0,6	20	M.105007	M.105009	M.105003	M.105009
10-40557-13	16	0,15÷0,6	26÷20	M.105001	M.105009	M.105003	M.105009
10-40557-15	16	0,75-1,0	18	M.105007	M.105009	M.105002	M.105009
10-40557-20	16	1-2	14	M.105007	M.105009	M.105002	M.105009
10-40557-22	16	2,5	/	M.105007	M.105009	M.105002	M.105009
10-40557-22L	16	2,5	/	M.105007	M.105012	M.105002	M.105012
10-40557-26	16	2,5-3,0	12	M.105007	M.105009	M.105002	M.105009
10-40557-32	16	/	32÷28	M.105007	M.105009	M.105003	M.105009
10-40561	12	2,5-3,0	12	M.105007	M.105009	M.105002	M.105009
10-40561-12	12	0,6	20	M.105007	M.105009	M.105003	M.105009
10-40561-15	12	0,75-1,0	18	M.105007	M.105009	M.105002	M.105009
10-40561-177	12	1,5	18-16	M.105007	M.105009	M.105002	M.105009
10-40561-20	12	2	14	M.105007	M.105009	M.105002	M.105009
10-40561-22	12	2,5	/	M.105007	M.105009	M.105002	M.105009
10-40561-30	12	4-5	/	M.105007	M.105009	M.105002	M.105009
10-40561-30M	12	4	/	M.105007	M.105009	M.105002	M.105009
10-40561-38	12	6	10	M.105007	M.105009	M.105002	M.105009

Please consult our sales department for other contact options or crimp tooling details.



CONNECTOR CONTACTS IT - ITS - ITS-RG - ITZ Connectors



Pin Crimp Contacts - Manual and Pneumatic Tools

A

Manual and Pneumatic Tools Table										
Part Number	Contact Size	Wire Size		Manual Crimp Tool		Pneumatic Tool Type "B"			Oleodinamic Tool	
		mm ²	AWG	Manual Tool	Turret	Pneumatic Tool	Die	Locator	Oleodinamic Tool	Die
10-40792	8	9	8	/	/	M.112000	M.112001	M.112309	M.112004	M.112005
10-40792-15	8	0,75-1,0	18	M.105028	M.104002	/	/	/	/	/
10-40792-18	8	1÷2	18÷14	M.105028	M.104002	/	/	/	/	/
10-40792-20	8	2	14	M.105028	M.104002	/	/	/	/	/
10-40792-26	8	3	12 -14	M.105028	M.104002	/	/	/	/	/
10-40792-30	8	4-5	/	M.105028	M.104002	/	/	/	M.112004	M.112008
10-40792-38	8	6	10	/	/	M.112000	M.112001	M.112309	M.112004	M.112005
10-40792-50	8	10	/	/	/	M.112000	M.112001	M.112309	M.112004	M.112005
10-40792-58	8	13,2	6	/	/	M.112000	M.112001	M.112309	M.112004	M.112005
10-113474-4P	4	25	4	/	/	M.112000	M.112002	M.112311	M.112004	M.112006
10-113474-4P-22	4	2,5	/	/	/	/	/	/	M.112004	M.112009
10-113474-4P-26	4	3	/	/	/	/	/	/	M.112004	M.112009
10-113474-4P-30	4	4-5	/	/	/	/	/	/	M.112004	M.112008
10-113474-4P-38	4	6	10	/	/	M.112000	M.112001	M.112311	M.112004	M.112005
10-113474-4P-50	4	10	/	/	/	M.112000	M.112001	M.112311	M.112004	M.112005
10-113474-4P-58	4	13,2	6	/	/	M.112000	M.112001	M.112311	M.112004	M.112005
10-113474-4P-62	4	16	/	/	/	M.112000	M.112002	M.112311	M.112004	M.112006
10-113474-1P	0	50-60	0	/	/	M.112000	M.112003	M.112313	M.112004	M.112010
10-113474-1P-107	0	50	/	/	/	M.112000	M.112003	M.112313	M.112004	M.112010
10-113474-1P-72	0	22-25	4	/	/				M.112004	M.112006
10-113474-1P-35	0	35	/	/	/	/	/	/	M.112004	M.112007
10-113474-1P-45	0	9	8	/	/				M.112004	M.112005
10-113474-1P-50	0	10	/	/	/				M.112004	M.112005
10-113474-1P-58	0	13,2	6	/	/				M.112004	M.112005
10-113474-1P-62	0	16	/	/	/				M.112004	M.112006
10-113474-0P	4/0	107	4/0	/	/	/	/	/	M.105013	M.112012
10-113474-0P-78	4/0	25	/	/	/	/	/	/	M.112004	M.112006
10-113474-0P-107	4/0	50	/	/	/	/	/	/	M.112004	M.112010
10-113474-0P-144	4/0	70	/	/	/	/	/	/	M.105013	M.105053

Please consult our sales department for other contact options or crimp tooling details.

Manual and Pneumatic Tools				
				
Pneumatic Crimp Tool Type "B"	Die For Pneumatic Crimp Tool Type "B"	Locator for Pneumatic Crimp Tool Type "B"	Oleodinamic Crimp Tool	Die for Oleodinamic Crimp Tool