


# ABC 54705 Replacement Fiber Optic Test Probe Jumper Simplex



**Fiber optic test probe for fast and easy optical analysis of installed fiber optic systems**

### How To Order

Table I: Fiber Size	
Symbol	Size
A	100/140 $\mu$ m
B	62.5/125 $\mu$ m
C	50/125 $\mu$ m
D	200/230 $\mu$ m
E	Singlemode 9.3/125
F	Customer Defined
G	SM 5.8/125 M/F DIA. .21na
H	SM 7.5/125 M/F DIA. .17na




Optical insertion loss  $\leq$  1.0 dB @  
850 or 1300 nm wavelength.  
Glenair Fiber Optic Test Probe U.S.  
Patent Number 5,960,137.

- Connector Type:**  
**A** = ST Connector  
**B** = FC Connector  
**C** = SC Connector  
**D** = FC/APC Connector  
**E** = Customer Defined  
**F** = LC Connector  
**G** = SC/APC Connector  
**H** = M29504/04 Pin  
**J** = M29504/05 Socket

**F** = Flat Polish  
**C** = Concave Polish  
*(Probe end only. Omit for standard "PC" physical contact polish)*

Standard Tolerance	
Length	Tolerance
5 in, up to 2 ft	+1/-0 in
Over 2 ft, up to 10 ft	+3/-0 in
Over 10 ft, up to 50 ft	+6/-0 in
Over 50 ft, up to 100 ft	+1/-0 ft
Over 100 ft	+2/-0 ft



## Fiber optic polishing tool for fiber optic test probes



### How To Order

