

HIGH-TEMPERATURE, MICRO MINIATURE CIRCULAR

Series 806

Mil-Aero Connectors

120-100 Helical Polymer-Core Convoluted Tubing



OUTSTANDING MECHANICAL WIRE PROTECTION AND LUBRICITY FOR NON-ENVIRONMENTAL AND NON-EMI/RFI APPLICATIONS, IAW SAE AS81914



How To Order ThermaRex Series 806 Mil-Aero Jam-nut Receptacle								
SAMPLE PART NUMBER		120-100	-1	-1	-16	B	R	L
Series / Basic Part No.	120-100 300°C ThermaRex polymer-core Conduit							
Class	1 = Standard Wall 2 = Thin Wall							
Convolution	1 = Standard 2 = Close							
Tubing Size	See table 1							
Color	B = Black C = Clear O = Orange BL = Blue Y = Yellow							
Material	R = High Temperature ThemaRex, 300°C							
Lanyard	L = Lanyard; omit for none							




Table I: Tubing Size Order Number and Dimensions

Tubing Size	Fractional Size Ref	A Inside Dia Min	B Dia Max	Min Bend Radius
06	3/16	.181 (4.6)	.320 (8.1)	.50 (12.7)
09	9/32	.273 (6.9)	.414 (10.5)	.75 (19.1)
10	5/16	.306 (7.8)	.450 (11.4)	.75 (19.1)
12	3/8	.359 (9.1)	.510 (13.0)	.88 (22.4)
14	7/16	.427 (10.8)	.571 (14.5)	1.00 (25.4)
16	1/2	.480 (12.2)	.650 (16.5)	1.25 (31.8)
20	5/8	.603 (15.3)	.770 (19.6)	1.50 (38.1)
24	3/4	.725 (18.4)	.930 (23.6)	1.75 (44.5)
28	7/8	.860 (21.8)	1.073 (27.3)	1.88 (47.8)
32	1	.970 (24.6)	1.226 (31.1)	2.25 (57.2)
40	1 1/4	1.205 (30.6)	1.539 (39.1)	2.75 (69.9)
48	1 1/2	1.437 (36.5)	1.832 (46.5)	3.25 (82.6)
56	1 3/4	1.688 (42.9)	2.156 (54.8)	3.63 (92.2)
64	2	1.937 (49.2)	2.332 (59.2)	4.25 (108.0)

PACKAGING

- Long-length orders of 120-100 conduit are subject to carrier weight and box size restrictions. For example, UPS air shipments are currently limited to 50 lbs. per box. Unless otherwise specified, Glenair standard practice is to ship optimal lengths of product based on weight, size, and individual carrier specifications.
- Consult factory for thin-wall, close convolution combination and for PEEK™ and PTFE min/max dimensions.