




710-930 Guardian Transition Aluminum Transition for Annular Convulved Tubing

Guardian Transition for Glenair Annular Convulved Tubing



Notes

- Annular convulved tubing shown for reference only. Tubing to be ordered sparately. see Glenair drawings 120-001, 120-125 and 120-137.
- Glenair Assembly procedure AP74-010 is recommended for adapter to conduit termination.
- Conduit Retaining clip and conduit O-rings to be supplied un-assembled.
- Glenair 600 series backshell assembly tools are recommended for assembly and installation.
- Material/Finish:
 - Transition - aluminum alloy/see table III
 - Hardware - cress/passivate
 - retaining clip - high grade engineering thermoplastic/N.A.

Dash No	Entry A	Entry B	Entry C	Entry D
01	09	09	09	N/A
03	14	12	12	N/A
04	28	24	14	N/A
05	28	24	24	N/A
06	24	12	12	20
07	20	12	12	12
08	12	09	09	09
09	28	14	24	N/A
10	24	20	12	12

Entry Size	A Dia.		B Dia Max	Shrink Boot Ref
	Min	Max		
-09	.24	.28	.63	770-001S103
-12	.33	.37	.73	770-001S104
-14	.40	.44	.79	770-001S104
-20	.57	.62	.98	770-001S105
-24	.69	.75	1.15	770-001S106
-28	.81	.87	1.27	770-001S107

Sym	Finish Description
N	Cadmium plate/olive drab over nickel
NF	CAD/ O.D. over electroless nickel (1000 hour salt spray)
M	Electroless nickel

710-930 Guardian Transition Aluminum Transition for Annular Convuluted Tubing



Special Applications

