



## ITS Bayonet Connector Assemblies Pin Crimp Contacts Manual and Pneumatic Tools

**TABLE I: MANUAL AND PNEUMATIC TOOLS PART NUMBERS, SIZE & DIMENSIONS**

PART NUMBER	CONTACT SIZE	WIRE SIZE		MANUAL CRIMP TOOL		MANUAL CRIMP TOOL (GF8 M.105062 special crimp tool for Glenair contacts)		PNEUMATIC TOOL TYPE "A"	
		mm <sup>2</sup>	AWG	MANUAL TOOL	TURRET	MANUAL TOOL	TURRET	PNEUMATIC TOOL	TURRET
10-375-20	20	0,15-0,6	26-20	M.105001	M.105026	---	---	M.105003	M.105026
10-40579	18	0,15-0,6	26-20	M.105001	M.105025	---	---	M.105003	M.105025
10-40553	16S	1-1,5	18-16	M.105007	M.105009	M.105062	GP1800	M.105002	M.105009
10-40553-12	16S	0,6	20	M.105007	M.105009	M.105062	GP1800	M.105002	M.105009
10-40553-13	16S	0,15-0,6	26-20	M.105001	M.105009	M.105001	GP1800	M.105003	M.105009
10-40553-15	16S	0,75-1,0	18	M.105007	M.105009	M.105062	GP1800	M.105002	M.105009
10-40553-20	16S	1-2	14	M.105007	M.105009	M.105062	GP1800	M.105002	M.105009
10-40553-26	16S	3	12	M.105007	M.105009	M.105062	GP1800	M.105002	M.105009
10-40557	16	1-1,5	18-16	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40557-08	16	0,15-0,2	26-24	M.105001	M.105009	---	---	M.105003	M.105009
10-40557-12	16	0,6	20	M.105001	M.105009	M.105062	M.105063	M.105003	M.105009
10-40557-13	16	0,15-0,6	26-20	M.105001	M.105009	M.105062	M.105063	M.105003	M.105009
10-40557-15	16	0,75-1,0	18	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40557-20	16	1-2	14	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40557-22	16	2,5	/	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40557-22L	16	2,5	/	M.105007	M.105012	M.105062	M.105063	M.105002	M.105012
10-40557-26	16	3	12	M.105007	M.105009	---	---	M.105002	M.105009
10-40557-32	16	/	32-28	M.105001	M.105009	M.105062	M.105063	M.105003	M.105009
10-40561	12	2,5-3,5	12	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40561-12	12	0,6	20	M.105001	M.105009	M.105062	M.105063	M.105003	M.105009
10-40561-15	12	0,75-1,0	18	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40561-177	12	1,5	18-16	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40561-20	12	1-2	18-14	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40561-22	12	2,5	/	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40561-30	12	4-5	/	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40561-30M	12	4	/	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40561-38	12	6	10	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009

Please consult our sales department for other contact options or crimp tooling details.



Manual Crimp Tool



Turret for Manual Crimp Tool



Pneumatic Crimp Tool Type "A"



Turret for Pneumatic Crimp Tool Type "A"

ITS Bayonet Connector Assemblies  
Pin Crimp Contacts  
Manual and Pneumatic Tools



TABLE I: MANUAL AND PNEUMATIC TOOLS PART NUMBERS, SIZE & DIMENSIONS

PART NUMBER	CONTACT SIZE	WIRE SIZE		MANUAL CRIMP TOOL		PNEUMATIC TOOL TYPE "B"			OLEODINAMIC TOOL	
		mm <sup>2</sup>	AWG	MANUAL TOOL	TURRET	PNEUMATIC TOOL	DIE	LOCATOR	OLEODINAMIC TOOL	DIE
10-40792	8	9	8	/	/	M.112000	M.112001	M.112309	M.112004	M.112005
10-40792-15	8	0,75-1,0	18	M.105028	M.104002	/	/	/	/	/
10-40792-18	8	1÷2	18÷14	M.105028	M.104002	/	/	/	/	/
10-40792-20	8	2	14	M.105028	M.104002	/	/	/	/	/
10-40792-26	8	2,5-3,0	12	M.105028	M.104002	/	/	/	/	/
10-40792-30	8	4-5	/	M.105028	M.104002	/	/	/	M.112004	M.112008
10-40792-38	8	6	10	/	/	M.112000	M.112001	M.112309-1	M.112004	M.112005
10-40792-50	8	10	/	/	/	M.112000	M.112001	M.112309-1	M.112004	M.112005
10-40792-58	8	13,2	6	/	/	M.112000	M.112001	M.112309-1	M.112004	M.112005
10-113474-4P	4	25	4	/	/	M.112000	M.112002	M.112311	M.112004	M.112006
10-113474-4P-22	4	2,5	/	/	/	/	/	/	M.112004	M.112009
10-113474-4P-26	4	2,5-3,0	12	/	/	/	/	/	M.112004	M.112009
10-113474-4P-30	4	4-5	/	/	/	/	/	/	M.112004	M.112008
10-113474-4P-38	4	6	10	/	/	M.112000	M.112001	M.112311	M.112004	M.112005
10-113474-4P-50	4	10	/	/	/	M.112000	M.112001	M.112311	M.112004	M.112005
10-113474-4P-58	4	13,2	6	/	/	M.112000	M.112001	M.112311	M.112004	M.112005
10-113474-4P-62	4	16	/	/	/	M.112000	M.112002	M.112311	M.112004	M.112006
10-113474-1P	0	50-60	0	/	/	M.112000	M.112003	M.112313	M.112004	M.112010
10-113474-1P-107	0	50	/	/	/	M.112000	M.112003	M.112313	M.112004	M.112010
10-113474-1P-72	0	22-25	4	/	/				M.112004	M.112006
10-113474-1P-35	0	35	/	/	/	/	/	/	M.112004	M.112007
10-113474-1P-45	0	9	8	/	/				M.112004	M.112005
10-113474-1P-50	0	10	/	/	/				M.112004	M.112005
10-113474-1P-58	0	13,2	6	/	/				M.112004	M.112005
10-113474-1P-62	0	16	/	/	/				M.112004	M.112006
10-113474-0P	4/0	107	4/0	/	/	/	/	/	M.105013	M.112012
10-113474-0P-78	4/0	25	/	/	/	/	/	/	M.112004	M.112006
10-113474-0P-107	4/0	50	/	/	/	/	/	/	M.112004	M.112010
10-113474-0P-144	4/0	70	/	/	/	/	/	/	M.105013	M.105053

Please consult our sales department for other contact options or crimp tooling details.



Pneumatic Crimp Tool  
Type "B"



Die For Pneumatic  
Crimp Tool Type "B"



Locator for Pneumatic  
Crimp Tool Type "B"



Oleodinamic Crimp Tool



Die for  
Oleodinamic Crimp Tool

### TABLE I: MANUAL AND PNEUMATIC TOOLS PART NUMBERS, SIZE & DIMENSIONS

PART NUMBER	CONTACT SIZE	WIRE SIZE		MANUAL CRIMP TOOL		MANUAL CRIMP TOOL (GF8 M.105062 special crimp tool for Glenair contacts)		PNEUMATIC TOOL TYPE "A"	
		mm <sup>2</sup>	AWG	MANUAL TOOL	TURRET	MANUAL TOOL	TURRET	PNEUMATIC TOOL	TURRET
10-40520LC	20	0,15-0,6	26-20	M.105001	M.105026	---	---	M.105003	M.105026
10-40588	18	0,15-0,6	26-20	M.105001	M.105025	---	---	M.105003	M.105025
10-40552	16S	1-1,5	18-16	M.105007	M.105009	M.105062	GP1800	M.105002	M.105009
10-40552-12	16S	0,6	20	M.105007	M.105009	M.105062	GP1800	M.105002	M.105009
10-40552-13	16S	0,15-0,6	26-20	M.105001	M.105009	---	---	M.105003	M.105009
10-40552-15	16S	0,75-1	18	M.105007	M.105009	M.105062	GP1800	M.105002	M.105009
10-40552-20	16S	1-2	14	M.105007	M.105009	M.105062	GP1800	M.105002	M.105009
10-40552-26	16S	2,5-3,0	12	M.105007	M.105009	M.105062	GP1800	M.105002	M.105009
10-40556	16	1-1,5	18-16	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40556-08	16	0,15-0,2	26-24	M.105001	M.105009	M.105062	M.105063	M.105003	M.105009
10-40556-12	16	0,6	20	M.105001	M.105009	M.105062	M.105063	M.105003	M.105009
10-40556-13	16	0,15-0,6	26-20	M.105001	M.105009	M.105062	M.105063	M.105003	M.105009
10-40556-15	16	0,75-1	18	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40556-20	16	1-2	14	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40556-22	16	2,5	/	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40556-26	16	2,5-3,0	12	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40556-32	16	/	32-28	M.105001	M.105009	M.105062	M.105063	M.105003	M.105009
10-40560	12	2,5-3,0	12	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40560-12	12	0,6	20	M.105001	M.105009	M.105062	M.105063	M.105003	M.105009
10-40560-15	12	0,75-1	18	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40560-177	12	1,5	18-16	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40560-20	12	2	14	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40560-22	12	2,5	/	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40560-30	12	4-5	/	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40560-30M	12	4	/	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009
10-40560-38	12	6	10	M.105007	M.105009	M.105062	M.105063	M.105002	M.105009

Please consult our sales department for other contact options or crimp tooling details.



Manual Crimp Tool



Turret for  
Manual Crimp Tool



Pneumatic Crimp Tool  
Type "A"



Turret for Pneumatic  
Crimp Tool Type "A"

ITS Bayonet Connector Assemblies  
Socket Crimp Contacts  
Manual and Pneumatic Tools




TABLE I: MANUAL AND PNEUMATIC TOOLS PART NUMBERS, SIZE & DIMENSIONS

PART NUMBER	CONTACT SIZE	WIRE SIZE		MANUAL CRIMP TOOL		PNEUMATIC TOOL TYPE "B"			OLEODINAMIC TOOL	
		mm <sup>2</sup>	AWG	MANUAL TOOL	TURRET	PNEUMATIC TOOL	DIE	LOCATOR	OLEODIN-AMIC TOOL	DIE
10-40793-1	8	9	8	/	/	M.112000	M.112001	M.112309	M.112004	M.112005
10-40793-1-15	8	0,75-1	18	M.105028	M.104002	/	/	/	/	/
10-40793-1-18	8	1-2	18-14	M.105028	M.104002	/	/	/	/	/
10-40793-1-20	8	2	14	M.105028	M.104002	/	/	/	/	/
10-40793-1-26	8	2,5-3,0	12	M.105028	M.104002	/	/	/	/	/
10-40793-1-30	8	4-5	/	M.105028	M.104002	/	/	/	M.112004	M.112008
10-40793-1-38	8	6	10	/	/	M.112000	M.112001	M.112309	M.112004	M.112005
10-40793-1-50	8	10	/	/	/	M.112000	M.112001	M.112309	M.112004	M.112005
10-10793-1-58	8	13,2	6	/	/	M.112000	M.112001	M.112309	M.112004	M.112005
10-113474-4S-1	4	25	4	/	/	M.112000	M.112002	M.112311	M.112004	M.112006
10-113474-4S-1-22	4	2,5	/	/	/	/	/	/	M.112004	M.112009
10-113474-4S-1-26	4	2,5-3,0	12	/	/	/	/	/	M.112004	M.112009
10-113474-4S-1-30	4	4-5	/	/	/	/	/	/	M.112004	M.112008
10-113474-4S-1-38	4	6	10	/	/	M.112000	M.112001	M.112311	M.112004	M.112005
10-113474-4S-1-50	4	10	/	/	/	M.112000	M.112001	M.112311	M.112004	M.112005
10-113474-4S-1-58	4	13,2	6	/	/	M.112000	M.112001	M.112311	M.112004	M.112005
10-113474-4S-62	4	16	/	/	/	M.112000	M.112002	M.112311	M.112004	M.112006
10-113474-1S	0	50-60	0	/	/	M.112000	M.112003	M.112313	M.112004	M.112010
10-113474-1S-107	0	50	/	/	/	M.112000	M.112003	M.112313	M.112004	M.112010
10-113474-1S-72	0	22-25	4	/	/	M.112000	M.112002	M.112313	M.112004	M.112006
10-113474-1S-35	0	35	/	/	/	/	/	/	M.112004	M.112007
10-113474-1S-45	0	9	8	/	/				M.112004	M.112005
10-113474-1S-50	0	10	/	/	/				M.112004	M.112005
10-113474-1S-58	0	13,2	6	/	/				M.112004	M.112005
10-113474-1S-62	0	16	/	/	/				M.112004	M.112006
10-113474-0S	4/0	107	4/0	/	/	/	/	/	M.105013	M.112012
10-113474-0S-78	4/0	25	/	/	/	/	/	/	M.112004	M.112006
10-113474-0S-107	4/0	50	/	/	/	/	/	/	M.112004	M.112010
10-113474-0S-144	4/0	70	/	/	/	/	/	/	M.105013	M.105053

Please consult our sales department for other contact options or crimp tooling details.



Pneumatic Crimp Tool  
Type "B"



Die for Pneumatic  
Crimp Tool Type "B"



Locator for Pneumatic  
Crimp Tool Type "B"



Oleodinamic Crimp Tool



Die for  
Oleodinamic Crimp Tool