



Series 79 Micro-Crimp Mateable, Recommended Panel Cut-Outs


ALL CUTOUTS FOR .063" (.070 MAX) THICK PANEL MOUNTING




Shell Size A




Shell Size B




Shell Size C




Shell Size D



Shell Size E



Shell Size F




Shell Size G




Series 79
Micro-Crimp Mateable, Hermetic Receptacles
Recommended Panel Cut-Outs

Series 79 Micro-Crimp Mateable, Recommended Panel Cut-Outs


ALL CUTOUTS FOR .063" (.070 MAX) THICK PANEL MOUNTING




Shell Size H




Shell Size J



Shell Size K



Shell Size L



Shell Size M