



964-009
Bulk Simplex Fiber Optic Cable
100/140 Graded Index (ETFE Jacket)



100/140 MULTIMODE GRADED INDEX FIBER OPTIC CABLE WITH ETFE JACKET



Cable Specifications	
Core/Mode Field Diameter	100 $\mu\text{m} \pm 4 \mu\text{m}$
Cladding Diameter	140 $\mu\text{m} \pm 3 \mu\text{m}$
Primary Buffer	500 $\mu\text{m} \pm 25 \mu\text{m}$
Secondary Buffer	900 $\mu\text{m} \pm 50 \mu\text{m}$
Jacket	.083 + .007 Inch Diameter
Attenuation: @ 850 nm @ 1300 nm	6.0 dB/km 4.0 dB/km
Bandwidth: @ 850 nm @ 1300 nm	100 Mhz/km Minimum 100 Mhz/km Minimum
Numerical Aperture	.290 + .015
Index Profile	Graded
Proof Test	>100 KPSI
Operating Temperature	-40° C to 85° C

Consult Factory for price in feet or meters and for Standard Length Tolerance

Kevlar® is a registered trademark of DuPont Company.

