


Series 33 NPT Adapters

for AS50151 Crimp, M26482 Series II, M83723 Series III, AS95234

330AS001, 330AS002 NPT Adapter, Spin Coupling



Adapter Code **A**

AS50151 crimp, AS95234, MIL-DTL-26482
Ser. II, MIL-DTL-83723 Ser. III


Spin coupling. NPT adapter fits AS50151 crimp (MS3450), AS95234, MIL-DTL-26482 Series II, MIL-DTL-83723 Series III connectors. Adapter has tapered ANSI/ASME B1.20.1 National Pipe Threads. Aluminum or stainless steel.

PART NUMBER

330AS001 M 16 04 -4


Base P/N	330AS001 External NPT 330AS002 Internal NPT
Material/Finish	M Alum/ Electroless Nickel MT Alum/ Nickel-PTFE NF Alum/ Olive Drab Cadmium ZR Alum/ Black Zinc-Nickel TZ Alum/ Tin-Zinc ZI SST/ Passivated
Shell Size	08 10 12 14 16 18 20 22 24 28 32 36 40
NPT Size	Code NPT Size 03 3/8 04 1/2 05 3/4 06 1 07 1 1/4 08 1 1/2 09 2
Length	-3 1.5 inches (NPT size 3/8 only) -4 2.0 inches (NPT size 3/8 to 1) -5 2.5 inches -6 3.0 inches <i>Length in 1/2 inch increments.</i>

330AS001 WITH EXTERNAL NPT



Shell Size	A Thread	Ø B Max.	
		in	mm
08	0.500-20 UNF	.65	16.5
10	0.625-24 UNEF	.77	19.6
12	0.750-20 UNEF	.94	23.9
14	0.875-20 UNEF	1.07	27.2
16	1.000-20 UNEF	1.21	30.7
18	1.0625-18 UNEF	1.23	31.2
20	1.1875-18 UNEF	1.36	34.5
22	1.3125-18 UNEF	1.48	37.6
24	1.4375-18 UNEF	1.73	43.9
28	1.750-18 UNS	1.97	50.0
32	2.000-18 UNS	2.22	56.4
36	2.250-16 UN	2.47	62.7
40	2.500-16 UN	2.72	69.1

330AS002 WITH INTERNAL NPT



Size Code	NPT Size	E		Ø F		Ø G	
		±.015 (0.4) in	±.015 (0.4) mm	±.015 (0.4) in	±.015 (0.4) mm	±.015 (0.4) in	±.015 (0.4) mm
03	3/8	.593	15.1	.675	17.1	.875	22.2
04	1/2	.781	19.8	.840	21.3	1.000	25.4
05	3/4	.812	20.6	1.050	26.7	1.250	31.8
06	1	1.000	25.4	1.315	33.4	1.500	38.1
07	1 1/4	1.031	26.2	1.660	42.2	1.750	44.5
08	1 1/2	1.031	26.2	1.900	48.3	2.125	54.0
09	2	1.062	27.0	2.375	60.3	2.500	63.5