

Series 44 Banding Backshells

for MIL-DTL-38999 Series III and IV Connectors

447H*531 Banding Backshell, Shrink Boot, Spanner Nut

Self-Locking



Self-locking. Impact resistant coupling nut. 447H*531 banding backshell fits MIL-DTL-38999 Series III/IV connectors. Impact resistant coupling nut has 2.8 mm spanner wrench holes. Anti-decoupling mechanism provides audible detented coupling and prevents backoff under high vibration. Attach shielding and overbraid sleeving to backshell with band strap (not supplied). Shrink boot (not supplied) adds strain relief and environmental protection. Aluminum or stainless steel with thermoplastic anti-decoupling spring and SST retainer ring.

Adapter Code H

This accessory fits these connectors:
MIL-DTL-38999 Series III and Series IV


TABLE 1: ENTRY SIZE

Entry Size	øE		øF		øG		Shell Sizes
	in	mm	in	mm	in	mm	
03	.185	4.7	.303	7.7	.480	12.2	09-15
04	.252	6.4	.370	9.4	.551	14.0	09-17
05	.311	7.9	.433	11.0	.610	15.5	09-21
06	.374	9.5	.496	12.6	.673	17.1	11-23
07	.437	11.1	.555	14.1	.736	18.7	11-25
08	.500	12.7	.618	15.7	.800	20.3	13-25
10	.626	15.9	.744	18.9	.925	23.5	15-25
12	.752	19.1	.866	22.0	1.051	26.7	17-25
14	.874	22.2	.992	25.2	1.173	29.8	19-25
16	1.004	25.5	1.118	28.4	1.300	33.0	21-25
18	1.126	28.6	1.240	31.5	1.425	36.2	23-25
20	1.252	31.8	1.366	34.7	1.551	39.4	25

TABLE 2: LENGTH CODE

Length Code	J		K Max		L Max	
	in	mm	in	mm	in	mm
A	.291	7.4	1.035	26.3	1.362	34.6
B	.606	15.4	1.350	34.3	1.677	42.6
C	.803	20.4	1.547	39.3	1.874	47.6
D	1.197	30.4	1.941	49.3	2.768	57.6

FIGURE 1: SLOT OPTION (L)




Entry Size	Slot Length in	Slot Length mm
03, 04, 05	.157	4.0
06, 07, 08	.276	7.0
10, 12	.433	11.0
14, 16	.472	12.0
18, 20	.551	14.0

PART NUMBER

	447HS531	ZI	19	10	B	L	-157				
Base P/N	Base Part No.	Profile									
	447HS531	S Straight									
Material/Finish	447HJ531	J 90°									
	M	Alum/ Electroless Nickel									
	MT	Alum/ Nickel-PTFE									
	NF	Alum/ Olive Drab Cadmium									
	ZR	Alum/ Black Zinc-Nickel									
Shell Size	TZ	Alum/ Tin-Zinc									
	ZI	SST/ Passivated									
	Shell Size	Shell Size	9	11	13	15	17	19	21	23	25
	Size Code	09	11	13	15	17	19	21	23	25	
Entry Size	See Table 1										
Length	Applies to Profile S only. See Table 2.							A B C D			
Slot	Omit if not required. See Figure 1.							L Slots for Individual Shields			
Teflon Coating	Omit if not required.							-157 Teflon Coating on Inside Surface			

S Straight

J 90°



Shell Size	A Thread	øB Max in	øB Max mm	øD Min in	øD Min mm	M Max in	M Max mm	N Max in	N Max mm	Max Entry Size
9 (A)	M12X1.0-6H	.858	21.8	.264	6.7	.553	14.1	1.222	31.1	05
11 (B)	M15X1.0-6H	.984	25.0	.380	9.7	.622	15.8	1.347	34.2	07
13 (C)	M18X1.0-6H	1.157	29.4	.494	12.6	.683	17.4	1.494	38.0	08
15 (D)	M22X1.0-6H	1.280	32.5	.620	15.6	.744	18.9	1.561	40.0	10
17 (E)	M25X1.0-6H	1.406	35.7	.746	19.0	.799	20.3	1.624	41.3	12
19 (F)	M28X1.0-6H	1.516	38.5	.833	21.1	.846	21.5	1.722	43.8	14
21 (G)	M31X1.0-6H	1.642	41.7	.959	24.4	1.047	26.6	1.847	46.9	16
23 (H)	M34X1.0-6H	1.768	44.9	1.081	27.5	.969	24.6	1.972	50.1	18
25 (J)	M37X1.0-6H	1.890	48.0	1.207	30.7	1.047	26.6	2.098	53.3	20