



Swing-Arm® Clamps

for AS50151 Crimp, M26482 Series II, M83723 Series III, AS95234

870A001 Swing-Arm Saddle Clamp


Self-Locking



Self-locking, adjustable arms. 870A001 Swing-Arm saddle clamp fits AS50151 crimp, AS95234, MIL-DTL-26482 Series II, and MIL-DTL-83723 Series III connectors. Use with unshielded wire bundles. Adjustable arms pivot to 0°, 45° or 90° positions. Arms have self-locking threaded inserts to withstand high vibration. Full radius saddles have self-locking clinch nuts. Available in two clamp sizes: standard clamp fits most wire bundles, large clamp has increased clearance for oversize wire bundles. Coupling nut has anti-decoupling mechanism for audible detented coupling and prevents backoff under high vibration. Available in composite, aluminum or stainless steel.

Adapter Code A
AS50151 crimp, AS95234, MIL-DTL-26482 Ser. II, MIL-DTL-83723 Ser. III


ALUMINUM AND SST VERSIONS



Aluminum and stainless steel versions have round knurled coupling nuts.

PART NUMBER

	870A001	XB	22	B
Base P/N	870A001			
Material/Finish	<i>Composite</i> XB No Finish (Black) <i>Aluminum</i> M Electroless Nickel NF Olive Drab Cadmium MT Nickel-PTFR TZ Tin-Zinc ZR Black Zinc-Nickel <i>Stainless Steel</i> ZI Passivated			
Shell Size	08 10 12 14 16 18 20 22 24			
Clamp Size	A Standard Clamp B Large Clamp			




Shell Size	A Thread Class 2B	øB Min in	mm	C Max in	mm	D Flats in	mm	E Max in	mm	F Max in	mm	G Max in	mm	H Max in	mm	J Max in	mm	K Ref. in	mm
08	0.500-20 UNF	.264	6.7	.812	20.6	.750	19.1	1.43	36.3	1.35	34.3	.78	19.8	.91	23.1	.87	22.1	.393	10.0
10	0.625-24 UNEF	.365	9.3	.938	23.8	.875	22.2	1.50	38.1	1.45	36.8	.87	22.1	.94	23.9	.96	24.4	.455	11.6
12	0.750-20 UNEF	.498	12.6	1.125	28.6	1.000	25.4	1.56	39.6	1.60	40.6	.97	24.6	1.12	28.4	1.03	26.2	.598	15.2
14	0.875-20 UNEF	.575	14.6	1.250	31.8	1.125	28.6	1.57	39.9	1.68	42.7	1.02	25.9	1.21	30.7	1.10	27.9	.710	18.0
16	1.000-20 UNEF	.700	17.8	1.375	34.9	1.250	31.8	1.66	42.2	1.78	45.2	1.09	27.7	1.29	32.8	1.16	29.5	.839	21.3
18	1.0625-18 UNEF	.779	19.8	1.500	38.1	1.375	34.9	1.66	42.2	1.86	47.2	1.14	29.0	1.39	35.3	1.22	31.0	.934	23.7
20	1.1875-18 UNEF	.904	23.0	1.625	41.3	1.500	38.1	1.81	46.0	2.02	51.3	1.24	31.5	1.50	38.1	1.29	32.8	1.068	27.1
22	1.3125-18 UNEF	1.029	26.1	1.750	44.5	1.625	41.3	1.84	46.7	2.09	53.1	1.30	33.0	1.57	39.9	1.36	34.5	1.197	30.4
24	1.4375-18 UNEF	1.144	29.1	1.875	47.6	1.750	44.5	2.00	50.8	2.20	55.9	1.45	36.8	1.64	41.7	1.55	39.4	1.323	33.6

Swing-Arm® Clamps

for AS50151 Crimp, M26482 Series II, M83723 Series III, AS95234

870A001 Swing-Arm Saddle Clamp

CLAMP DIMENSIONS



Standard Clamp							Large Clamp						
Shell Size	L Max		M Min		N Ref.		Shell Size	P Max		R Min		S Ref.	
	in	mm	in	mm	in	mm		in	mm	in	mm	in	mm
08	.98	24.9	.22	5.6	.265	6.7	08	.98	24.9	.33	8.4	.356	9.0
10	1.05	26.7	.27	6.9	.310	7.9	10	1.20	30.5	.45	11.4	.422	10.7
12	1.20	30.5	.35	8.9	.422	10.7	12	1.45	36.8	.62	15.7	.637	16.2
14	1.30	33.0	.47	11.9	.538	13.7	14	1.54	39.1	.68	17.3	.707	18.0
16	1.44	36.6	.55	14.0	.590	15.0	16	1.60	40.6	.80	20.3	.759	19.3
18	1.56	39.6	.62	15.7	.660	16.8	18	1.73	43.9	.90	22.9	.841	21.4
20	1.69	42.9	.70	17.8	.744	18.9	20	1.95	49.5	1.05	26.7	.996	25.3
22	1.77	45.0	.78	19.8	.826	21.0	22	2.08	52.8	1.18	30.0	1.060	26.9
24	1.89	48.0	.85	21.6	.896	22.8	24	2.32	58.9	1.30	33.0	1.124	28.5

MATERIAL/FINISH

Composite (Code XB)

Coupling nut, body, arms, saddles:
polyetherimide (PEI), unplated

Screws, washers, inserts: stainless steel/
passivated

Anti-decoupling springs: thermoplastic
Clinch Nuts: stainless steel, silver plated

Aluminum (Codes M, MT, NF, TZ, ZR)

Coupling nut, body, arms, saddles: aluminum
Screws, washers, inserts: stainless steel/
passivated

Anti-decoupling springs: thermoplastic
Clinch Nuts: Codes M, MT, TZ and ZR:
stainless steel, silver plated.

Code NF: stainless steel/ olive drab cadmium

Stainless Steel (Code Z1)

Coupling nut, body, arms, saddles: SST
Screws, washers, inserts: stainless steel/
passivated

Anti-decoupling springs: stainless steel
Clinch Nuts: stainless steel, silver plated