

A Complete Range of Fiber Optic Cable and Cable Protection Products

Well designed fiber optic connection systems begin with high-reliability single and multimode cable. Glenair is able to fabricate and supply a targeted range of fiber media—all available without expensive minimum length requirements. The goal of of fiber media shop is to provide a fast-turn supply of specialty F/O media for use in our own cable assemblies, customer prototype projects and other short-run, limited bulk length applications.

Nobody can beat Glenair when it comes to providing fiber optic media with rugged and yet flexible media protection. We are absolute experts in this field and can suggest and supply everything from jacketed cable resistant to fuel exposure to crush-proof polymer-core conduit solutions. And because we make and stock all the component parts ourselves, we can offer lightning-fast turnaround on even highly specialized requirements.



Product No.	Description	Page No.
Bulk Extruded Fiber Optic Cable		
ABC 3586	Bulk Simplex Fiber Optic Cable, 9.3/125 Singlemode Stepped Index	K-2
ABC 3580	Bulk Simplex Fiber Optic Cable, 50/125 Graded Index	K-3
ABC 3569	Bulk Simplex Fiber Optic Cable, 62.5/125 Graded Index	K-4
ABC 3821	Bulk Simplex Fiber Optic Cable, 62.5/125 Graded Index (ETFE Jacket)	K-5
ABC 3571	Bulk Simplex Fiber Optic Cable, 100/140 Graded Index	K-6
MIL-T-81914 Convoluted Tubing		
120-100	Series 74 Helical Convoluted Tubing	K-7
120-103	Series 74 Helical Convoluted Tubing with Braid	K-8
120-108/120-132	Standard and Ultra Small Diameter PEEK Helical Convoluted Tubing	K-9

Catalog Notes For all parts in this catalog:

All parts, packages, and spools will be identified with manufacturer's name and part number, space permitting. Metric dimensions appear in parentheses in diagrams and tables, based on 1 inch = 25.4 mm, for reference only. Unless otherwise specified, the following other dimensional tolerances apply:

.xx = ± .03 (0.8) • .xxx = ± .015 (0.4) • Angles = ± 5°