



ABC 3586
Bulk Simplex Fiber Optic Cable
9.3/125 Singlemode Stepped Index

9.3/125 Singlemode graded index fiber optic cable



Cable Specifications	
Core/Mode Field Diameter	9.3 μm ± 3 μm
Cladding Diameter	125 μm ± 2 μm
Primary Buffer	500 μm ± 25 μm
Secondary Buffer	900 μm ± 50 μm
Jacket	.083 ± .007 Inch Diameter
Attenuation:	
@ 1310 nm	3.0 dB/km
@ 1550 nm	2.0 dB/km
Numerical Aperture	.110 + .020
Index Profile	Stepped
Proof Test	>100 KPSI
Operating Temperature	-40° C to +85° C

Consult Factory for price in feet or meters and for
Standard Length Tolerance

K

Kevlar[®] is a registered trademark of DuPont Company.