







**240-383P****Plugs****Page
B-30****240-383Q*****New!* Plugs with Crimp
Removable Contacts****Page
B-32****240-383W****Wall Mount Receptacles****Page
B-34****240-383J****Jam Nut Receptacles****Page
B-36****240-383R****Wall Mount Receptacles
with Crimp Removable Contacts****Page
B-38****240-383S****Jam Nut Receptacles
with Crimp Removable Contacts****Page
B-40****240-383D****Dual Flange Wall Mount Receptacles
with PC Tails****Page
B-42****240-383E****Dual Flange Jam Nut Receptacles
with PC Tails****Page
B-44****240-383B****Connector Adapters****Page
B-46**

Dimensions in inches (millimeters) and are subject to change without notice.