



A

Performance Specifications			
Description	Requirement	Procedure	
Current Rating	Contact Size	EIA-364-70 Method 1 IEC-60512-5 Test 9b	
	Max Current		
	8		40
	20		7.5
	22	5	
Shell-to-Shell Resistance (connectors with ground springs)	2.5 milli-volt drop maximum	EIA-364-83 IEC-60512-2-6 Electroless nickel plated connectors.	
Shielding Effectiveness	Frequency GHz	EIA-364-66 IEC-60512-23-3 Pin Connector with Optional Grounding Spring, Electroless nickel plated shells	
	Min Attenuation (dB)		
	0.1		100
	0.4		90
	0.8		85
	1.0		80
	3.0		55
	6.0		40
10.0	30		