series 28 HiPer-D[®] Standard and High-Density Connectors



280-031S float mount socket connectors for blind mating, crimp termination



280-0315 HiPer-D[®] socket connectors feature stainless steel floating bushings for blind mate applications. Attach to panel with #4-40 screws (not supplied with connector). Crimp, rear-releaseable size #20 or #22 contacts. Intermateable with standard M24308-type D-Subminiature connectors, the HiPer-D[®] features a rugged machined aluminum shell and rubber grommet. Threaded holes on the rear of the connector allow attachment of HiPer-D[®] EMI backshells. Contacts are packaged with connector. Terminate contacts with crimp tools purchased separately. Glassreinforced thermoset epoxy insulators, copper alloy retention clips. Connector meets IP67 immersion requirement. 1000 VAC, 5 Amps (#22) or 7.5 Amps (#20).

Ordering Information						
Sample Part Number 280-0315				Z2	G	
Basic Part Number	c Part Number 280-031S					
Shell Size- Contact Arrangement	See Shell Size - Contact Arrangements Table		-			
Shell Finish ME = Electroless Nickel MT = Nickel-PTFE JF = Cadmium with Yellow Chromate Z2 = Gold Z1 = Passivated Stainless Steel						
Mating Hardware	N = No Hardware (supplied with #8-32 tapped holes) G = Male Guide Pins B = Female Guide Bushings					

Shell Size - Contact Arrangements				
Shell Size-	Contact Size and Qty			
Contact Arr.	#20	#22		
Standard Density				
1S9	9			
2S15	15			
3S25	25			
4S37	37			
5850	50			
High Density				
1H15		15		
2H26		26		
3H44		44		
4H62		62		
5H78		78		
6H104		104		
	1			

Mating Hardware			
N			
No Hardware			
#8-32 tapped hole			
000			
В			
Female Guide Bushings			
000			
G Male Guide Pins			

Materials and Finishes			
Shell	Aluminum alloy		
Contacts	Copper alloy, 50 microin. gold plated		
Insulators	Thermoset epoxy		
Retention Clips	Copper alloy		
Grommet	Fluorosilicone rubber		
Hardware	300 series stainless steel		

Specifications			
Current Rating	#22 5 AMPS, #20 7.5 AMPS		
Test Voltage	1000 VAC RMS		
Insulation Resistance	5000 megohms minimum		
Operating Temperature	-65° C. to +200° C.		
Ingress Protection	IP 67		
Shock	300 g.		
Vibration, Random	43.92 g.		


R

SERIES 28 HiPer-D[®] Standard and High-Density Connectors



280-031S float mount socket connectors for blind mating, crimp termination

280-031S DIMENSIONS



	4	4	E	3	C Basic		D Basic		
Shell Size	in ± .015	mm ± 0.38	in ± .015	mm ± 0.38	in.	mm	in	mm	
1	1.986	50.44	.494	12.55	.984	24.99	1.636	41.55	
2	2.314	58.78	.494	12.55	1.312	33.32	1.964	49.89	
3	2.854	72.49	.494	12.55	1.852	47.04	2.504	63.60	
4	3.502	88.95	.494	12.55	2.500	63.50	3.152	80.06	
5	3.408	86.56	.600	15.24	2.406	61.11	3.058	77.67	
6	3.502	88.95	.662	16.81	2.500	63.50	3.152	80.06	

NOTES

- HiPer-D[®] connectors are available with a wide variety of materials and finishes. See *About Series 28 HiPer-D[®] Shell Plating Options* for additional choices. Glenair offers the industry's widest selection of plating and material choices with no setup charge, no minimum order quantity and no schedule impact.
- 2. For panel cutout dimensions, refer to *Panel Cutouts and Printed Circuit Board Footprints*.
- 3. Connectors are supplied with crimp contacts per M39029. Contacts are not installed. Refer to *HiPer-D® Contacts and Crimp Tools* for contact part numbers, specifications, crimp tool information, and insertion/extraction tools.
- 4. HiPer-D[®] connectors meet the requirements of MIL-DTL-24308 and are intermateable with standard M24308-type D-Subminiature connectors with corresponding contact arrangements and type.
- 5. Additional electrical, mechanical and environmental specifications are listed in *HiPer-D[®] Product Specification*.