

**Selected MIL-DTL-26500 Type Glass Sealed Hermetic Receptacles—Popular Connector Designs Superseded by MIL-DTL-83723**

Glenair MIL-DTL-26500 Hermetic connectors are offered in either passivated stainless steel or fused tin over stainless steel, with glass insulators fused to the connector shell, and contacts meeting a leak rate of  $1 \times 10^{-7}$  cc/helium per second. Maximum design flexibility is built into the MIL-DTL-26500 hermetic connector— with a minimum of 2 to a maximum of 61 circuits per connector in a wide variety of contact arrangements IAW MIL-STD-1554.

Fluorosilicone elastomer interfacial and peripheral seals ensure positive sealing with plug connectors. Nickel-iron alloy 52 contacts—available in sizes 12, 16 and 20— depending on the layout chosen—offer a broad selection of insert arrangement options. Optional solder cup or eyelet contact terminations are standard. Contacts for other applications such as thermocouple or flex prints are also available.

Quick Selection Guide		
Part Number	Description	Page
	MIL-DTL-26500 Type Insert Arrangements	F-2
	MIL-DTL-26500 Type Insert Arrangements and Keyway Positions	F-3
	Glenair Hermetic Connector Products Special Leak Rate Mod Codes	F-4
	Glenair Hermetic Connector Products Space Grade Mod Codes	F-5
	MIL-DTL-26500 Type Materials and Finishes	F-6
	MIL-DTL-26500 Type Bayonet and Threaded Coupling and Electrical Service Data	F-7
<b>230-036</b> <b>MS27034H*B**</b>	MIL-DTL-26500 Type Bayonet Coupling Solder Flange Mount Receptacle	F-8
<b>230-038</b> <b>MS27034H*T**</b>	MIL-DTL-26500 Type Threaded Coupling Solder Flange Mount Receptacle	F-10
<b>230-039</b> <b>MS24265*B**</b>	MIL-DTL-26500 Type Bayonet Coupling Single Hole Mount Receptacle	F-12
<b>230-040</b> <b>MS24265H*T**</b>	MIL-DTL-26500 Type Threaded Coupling Single Hole Mount Receptacle	F-14
<b>230-041</b> <b>MS24264H*B**</b>	MIL-DTL-26500 Type Bayonet Coupling Square Flange Mount Receptacle	F-16
<b>237-165</b>	MIL-DTL-26500 Type Threaded Coupling Square Flange Mount Receptacle	F-18