



HiPer-D®: the ideal distributed replacement for big, bulky and expensive ARINC 600 type connectors.

SERIES 28

Hiper-D® Standard and High-Density Connectors

Glenair HiPer-D environmental connectors are intermateable with M24308/D-Sub style connectors featuring rugged one piece aluminum shells and optional EMI ground spring for improved signal integrity. Standard Density (#20) or High Density (#22) contacts are crimp terminated and rear releasable for easy replacement and offered on inline, rear panel mount and float mount connectors. Standard and low profile PC Board mount – straight and right angle – configurations are also available. 11 “standard” insert arrangements available. Mated connectors meet IP67 requirements.

Product Features

- Environmental, crimp removable rectangular connector
- Advanced temperature, vibration and EMC/electrical performance
- M24308/D-Sub intermateable
- Fits panel and PCB footprint of M24308 D-Sub products
- Available in all 11 “standard” insert arrangements
- Standard Density (#20) and High Density (#22)
- EMI spring
- High temperature thermoset epoxy insulators
- Optional guide pins for blind mating

STANDARD AND HIGH DENSITY HIPER-D® - CUTAWAY

