



**TG60**  
**Connector Wrench**  
 MIL-DTL-27599, MIL-DTL-38999 Series I



**TG60 - 15**  
 Basic Part Number      Shell size



**TABLE I: Shell Size and Dimensions**

| Shell Size | A Dim Ref    | B Dia Ref    | C Dia Ref   |
|------------|--------------|--------------|-------------|
| 9          | 1.250 (31.8) | .442 (11.2)  | .647 (16.4) |
| 11         | 1.250 (31.8) | .570 (14.5)  | .647 (16.4) |
| 13         | 1.250 (31.8) | .687 (17.4)  | .647 (16.4) |
| 15         | 2.000 (50.8) | .812 (20.6)  | .647 (16.4) |
| 17         | 2.000 (50.8) | .937 (23.8)  | .647 (16.4) |
| 19         | 2.000 (50.8) | 1.042 (26.5) | .647 (16.4) |
| 21         | 2.000 (50.8) | 1.167 (29.6) | .617 (15.7) |
| 23         | 2.000 (50.8) | 1.292 (32.8) | .617 (15.7) |
| 25         | 2.000 (50.8) | 1.417 (36.0) | .617 (15.7) |

**APPLICATION NOTES**

1. Metric dimensions (mm) are indicated in parentheses.
2. Material: Aluminum alloy with electroless nickel finish.



Dimensions in inches (millimeters) and are subject to change without notice.