













AS81703 SERIES 3 TYPE CONNECTORS

Backshells and Accessories



Selection guide

	Straight strain relief AS85049/118	page D-12
	90° strain relief AS85049/120	page D-13
	Straight strain relief AS85049/52	page D-14
	90° strain relief AS85049/51	page D-15
	Straight shrink boot adapter AS85049/60-1	page D-16
	Straight shrink boot adapter AS85049/60-2G	page D-17
	Straight crimp ring backshell and crimp ring AS85049/26-1 and MS3419	page D-18
	Backshell Crimp Ring AS85049/26-2	page D-19
	E-Nut (Self-Locking and Non-Self-Locking) AS85049/31, MS3416 and MIL-DTL-85723/15N	page D-20
	90° Environmental Backshell AS85049/9 and MS3188B	page D-21
	Straight EMI/RFI Environmental Backshell AS85049/10 and MS3437A	page D-22
	Straight Environmental Backshell AS85049/11 and MS3437B	page D-23

