




A

Series 88 SuperFly®: the ultimate nanominiature tactical connector

Ready for the toughest, smallest, and highest-speed applications you've got

Compact, ultralightweight SuperFly® connectors feature threaded or push-pull coupling, EMI shielding and IP67 ingress protection. Available in a variety of layouts and sizes for audio, video, communications and data applications, Series 88 connectors are ideal for man-portable electronics where size and weight are prime considerations. Available in ready-to-use cordsets and single-ended pigtails, Series 88 SuperFly® QDC and threaded SuperFly cordsets can ship with a variety of cabling options, including ultraflexible GhostWire or impedance-controlled twisted pairs for high-speed applications.

- IP67 immersion rated
- High-reliability contacts: 5 Amp, 3 Amp, and 1 Amp
- High shock and vibration
- Robust EMI shielding
- Designed for high speed data applications
- Pre-wired, epoxy-sealed cordsets
- Straight and 90° PC tail receptacles
- 27 Contact arrangements
- Front or rear panel mounting
- Aluminum or stainless steel
- Accepts #22 to #32 AWG wire
- Made-to-order multi-branch cables and assemblies



Rear-panel mount push-pull and threaded PCB receptacles, and AlphaLink flex jumpers now available


SUPPORTED CONTACTS



#23 AS39029 Type 5 Amp Crimp Contact




Micro 3 Amp TwistPin Contact




Nano 1 Amp TwistPin Contact



SuperFly® front and rear box panel mount receptacles



Series 880 QDC Plug



Series 880 QDC Receptacle