








470-015
StarShield™ EMI/RFI Shield Termination Backshell
for MIL-DTL-83723 Series I & III, 5015 MS400 Series, AS81703
Series 3, and MIL-C- 26482 Series 2





StarShield™ environmental backshell with self-locking coupling and rear end options



SYMBOL H
45°
Option - Typ



SYMBOL B
Banding Nut with Band



Dimensions in inches (millimeters) and are subject to change without notice.

470-015
StarShield™ EMI/RFI Shield Termination Backshell
 for MIL-DTL-83723 Series I & III, 5015 MS400 Series, AS81703
 Series 3, and MIL-C- 26482 Series 2



Table I: Dimensions

Order No.	Connector Shell Size				A Thread Class 2 B	B Max	C Dia Max	D Max	E Max
	MIL-DTL-83723 Series I & III	MIL-DTL-5015 MS3400 Series	AS81703 Series III	MIL-C-26482 Series II					
08	8	8S	-	8	1/2-20 UNF	.82(20.8)	.690 (17.5)	.750 (19.1)	1.000 (25.4)
10	10	10S, 10SL	-	10	5/8-24 UNEF	.94(23.9)	.850 (21.5)	.780 (19.8)	1.020 (26.0)
12	12	12, 12S	7	12	3/4-20 UNEF	1.06(26.9)	.890 (22.5)	.810 (20.6)	1.040 (26.5)
14	14	14, 14S	12	14	7/8-20 UNEF	1.17(29.7)	1.000 (25.4)	.830 (21.1)	1.080 (27.5)
16	16	16, 16S	19	16	1-20 UNEF	1.29(32.8)	1.120 (28.5)	.860 (21.8)	1.100 ((28.0)
18	18	18	27	18	1 1/16-18 UNEF	1.42(36.1)	1.240 (31.5)	.880 (22.4)	1.120 (28.5)
20	20	20	37	20	1 3/16-18 UNEF	1.54(39.1)	1.380 (35.0)	.910 (23.1)	1.140 (29.0)
22	22	22	-	22	1 5/16-18 UNEF	1.66(42.2)	1.500 (38.0)	.930 (23.6)	1.180 (30.0)
24	24	24	-	24	1 7/16-18 UNEF	2.01(51.1)	1.610 (41.0)	.940 (23.9)	1.220 (31.0)

Table I: Dimensions (Continued)

Order No.	F Max	G Max	J Thread Class 2 A	K ± .004 (.10)	Ferrule Quantity (See note 4)	
					Std.	Opt.
					08	.880 (22.4)
10	.960 (24.4)	1.200 (30.5)	5/8-24 UNEF	.531 (13.5)	2	-
12	1.000 (25.4)	1.260 (32.0)	3/4-20 UNEF	.591 (15.0)	3	-
14	1.070 (27.2)	1.320 (33.5)	7/8-20 UNEF	.709 (18.0)	5	-
16	1.130 (28.7)	1.380 (35.0)	1-20 UNEF	.827 (21.0)	6	7
18	1.180 (30.0)	1.440 (36.5)	1 1/16-18 UNEF	.945 (24.0)	7	-
20	1.250 (31.8)	1.520 (38.5)	1 3/16-18 UNEF	1.063 (27.0)	9	11
22	1.310 (33.3)	1.570 (40.0)	1 5/16-18 UNEF	1.181 (30.0)	10	13
24	1.360 (34.5)	1.630 (41.5)	1 7/16-18 UNEF	1.299 (33.0)	12	17

Table II: Material and Finish Options

Code	Material; Finish Description
M	Aluminum; electroless nickel
MT	Aluminum; nickel - PTFE
NF	Aluminum; CAD/O. D. over electroless nickel
ZN	Aluminum; zinc nickel/O. D. over electroless nickel
ZR	Aluminum; zinc nickel/black over electroless nickel (RoHS)
ZRC	Aluminum; zinc nickel over electroless nickel (RoHS)
Z1	Stainless steel; passivate
ZM	Stainless steel; electroless nickel

Table III: Shrink Boot

Shell Size	Shrink Boot Part Number
09	770-001S1 04
11	770-001S1 06
13	770-001S1 06
15	770-001S1 07
17	770-001S1 07
19	770-001S1 08
21	770-001S1 08
23	770-001S1 08
25	770-001S1 09

Material/Finish

Backshell, elbows, coupling and gland nut, compression ring and star	Aluminum alloy or CRES/Table II
Band	CRES/passivate

Notes:

1. Assembly identified with manufacturer's name, part number and date code, space permitting.
2. For effective grounding, connector with conductive finish should be used.
3. Glenair 600 Series Backshell Assembly Tools are recommended for assembly and installation.
4. Star not supplied with order number 09. Drilled star is available on order numbers 15-25 only. If optional ferrule quantity per Table I is selected, one split and one solid star will be supplied.
5. Self-locking functionality, eliminates lock-wire requirements.
6. Ferrule kit sold separately.
 687-764 ferrule and HST device kit
 687-809 ferrule and sealing device kit
 687-748 solder ferrule
 687-841-01 HST flex device

Dimensions in inches (millimeters) and are subject to change without notice.