



Backshells and Accessories

Overview	H-2
MS backshells and accessories	H-4
Interface standards	H-6
Swing-Arm assembly	H-26



310-045 H-8
Composite shrink boot adapter standard profile with self-locking rotatable coupling nut.



440-143 H-9
Composite EMI/RFI backshell with Qwik-Ty strain relief, banding platform, and shrink boot groove.




440-144 H-11
Composite micro banding backshell with shrink boot groove, and self-locking coupling.



470-017 H-13
StarShield™ EMI/RFI composite shield termination backshell.



320H*030 H-15
Extender backshell, self-locking. Straight, 45°, or 90° with extended radius angular function. For use with size 8 contacts.



440H*233 H-16
Banding backshell, self-locking. Straight, 45°, or 90° extended radius angular function. For use with size 8 contacts.



620HS090 H-18
Strain relief saddle clamp backshell, self-locking. For use with size 8 contacts.



440HS232 H-19
EMI/RFI strain relief saddle clamp backshell, self-locking. For use with size 8 contacts.



443H*042 H-20
EMI/RFI Environmental band-in-a-can, saddle clamp backshell. Straight, 45°, or 90° with extended radius angular function. For size 8 contacts.



770-003 H-22
Series 77 heat shrink boots.



870H001 H-24
Swing-Arm Saddle Clamp composite, aluminum, or stainless steel.



870H002 H-26
Swing-Arm Saddle Clamp composite, with braid sock and metallic interface ring for EMI shield termination.



870H005 H-28
Swing-Arm Saddle Clamp aluminum or stainless steel, with drop-in banding adapter.




871H004 H-30
Swing-Arm Flex Clamp composite, flexible arms, with drop-in banding adapter.




687-749 H-32
Banding Split Ring for use in Strain Relief Assembly Procedure.

MIL-DTL-38999 Series III Type


Product selection guide



667-448 H-34
ProSeal™ threaded closure seal, full environmental protective cover.



667-449 H-36
Pressure seal, dust and immersion resistant protective cover.



660-049 and 660-050 H-38
Composite protective covers.



239-200 H-40
Plug cover for 233-215 piston sealed connector.



660-121 H-41
Composite self-locking receptacle covers.



239-202 H-42
Thick jam nut for .125" panels



239-204 H-43
Flange gasket. Available in 14 material options.



239-205 H-44
Jam-nut O-ring. Available in 13 material options.