



# MICRO USB 2.0 Series 801 Mighty Mouse




## 801-084 and 801-085 Receptacle with USB Micro "AB" Female Interface to Crimp Removable Contacts



Receptacles and Rear View of Crimp Termination

How To Order				
Sample Part Number	801-084	-02 MUSB	-M	A
Series	801-084 = Shield Termination Porch 801-085 = Accessory Threads			
Shell Style <sup>1</sup>	02 = Square Flange Mount Receptacle 07 = Jam Nut Mount Receptacle			
Shell Material and Finish <sup>1</sup>	NF = AL/Cadmium, Olive Drab MT = AL/Nickel PTFE		M = AL/Electroless Nickel ZNU = AL/Black Zinc Nickel	
Alternate Key Positions <sup>1</sup>	A, B, C, D, E, F			


### 801-084-02 AND 801-085-02 SQUARE FLANGE



801-084-02 Receptacle with Shield Termination Porch

801-085-02 Receptacle with Accessory Threads

### 801-085-07 AND 801-085-07 JAM NUT



801-084-07 Receptacle with Shield Termination Porch

801-085-07 Receptacle with Accessory Threads

### NOTES

- See Section A for recommended panel, additional finishes and alternate keyway positions.
- Receptacle connectors mate with Glenair plugs 801-082, 801-083, 801-087 and 801-088
- Contacts are crimp type, and used in rear release retention system (809-001)

Wire Schematic				
Rear Grommet Side			Mating Side	
Label	Cable Color (Typ)		ID	Micro USB Pin Description
V	Red	1	VBUS (V)	
G	Black	2	D-	
D-	White	3	D+	
D+	Green	4	ID	
ID	None	5	GND (G)	

⏏ Ground