



**TABLE III: CABLE ENTRY**

Dash No.	D Max	E Max	F Max	G Ref	H Max	J Max	K - Cable Range	
							Min *	Max
03	1.031 (26.2)	1.375 (34.9)	.812 (20.6)	.135 (3.4)	.781 (19.8)	.812 (20.6)	.156 (4.0)	.219 (5.6)
04	1.031 (26.2)	1.375 (34.9)	.937 (23.8)	.203 (5.2)	.781 (19.8)	.937 (23.8)	.188 (4.8)	.312 (7.9)
06	1.031 (26.2)	1.375 (34.9)	1.062 (27.0)	.285 (7.2)	.781 (19.8)	1.062 (27.0)	.281 (7.1)	.438 (11.1)
08	1.031 (26.2)	1.375 (34.9)	1.188 (30.2)	.350 (8.9)	.781 (19.8)	1.188 (30.2)	.312 (7.9)	.531 (13.5)
10	1.094 (27.8)	1.437 (36.5)	1.312 (33.3)	.390 (9.9)	.844 (21.4)	1.312 (33.3)	.375 (9.5)	.625 (15.9)
12	1.219 (31.0)	1.437 (36.5)	1.562 (39.7)	.460 (11.7)	.875 (22.2)	1.562 (39.7)	.500 (12.7)	.750 (19.1)
16	1.219 (31.0)	1.562 (39.7)	1.750 (44.5)	.510 (13.0)	.875 (22.2)	1.750 (44.5)	.625 (15.9)	.938 (23.8)
20	1.344 (34.1)	1.812 (46.0)	2.250 (57.2)	.695 (17.7)	.969 (24.6)	2.250 (57.2)	.938 (23.8)	1.250 (31.8)
24	1.547 (39.3)	2.062 (52.4)	2.375 (60.3)	.715 (18.2)	1.188 (30.2)	2.375 (60.3)	1.000 (25.4)	1.375 (34.9)
28	1.547 (39.3)	2.062 (52.4)	2.625 (66.7)	.915 (23.2)	1.188 (30.2)	2.625 (66.7)	1.250 (31.8)	1.625 (41.3)
32	1.734 (44.0)	2.188 (55.6)	2.812 (71.4)	1.070 (27.2)	1.375 (34.9)	2.812 (71.4)	1.500 (38.1)	1.875 (47.6)

\* Not Applicable Styles B and E

**TABLE IV: CABLE ENTRY**

Dash No.	L Max	M Max	N - Cable Range	
			Min	Max
04	1.312 (33.3)	.957 (24.3)	.125 (3.2)	.312 (7.9)
06	1.312 (33.3)	1.145 (29.1)	.250 (6.4)	.437 (11.1)
08	1.312 (33.3)	1.332 (33.8)	.312 (7.9)	.562 (14.3)
10	1.312 (33.3)	1.332 (33.8)	.350 (8.9)	.625 (15.9)
12	1.344 (34.1)	1.551 (39.4)	.500 (12.7)	.750 (19.1)
16	1.438 (36.5)	1.770 (45.0)	.625 (15.9)	.937 (23.8)
20	1.625 (41.3)	2.113 (53.7)	.875 (22.2)	1.250 (31.8)
24	1.688 (42.9)	2.363 (60.0)	1.000 (25.4)	1.375 (34.9)
28	1.938 (49.2)	2.770 (70.4)	1.250 (31.8)	1.625 (41.3)
32	1.938 (49.2)	3.020 (76.7)	1.437 (36.5)	1.875 (47.6)

**See inside back cover fold-out or page 14 for Table II.**

1. Metric dimensions (mm) are indicated in parentheses.
2. Cable range is defined as the accommodations range for the wire bundle or cable. Dimensions shown are not intended for inspection criteria.
3. Style C saddles are bottomed on clamp ears.

**TABLE V: CABLE ENTRY**

Dash No.	P Max	R Max	S Max	T Max	W Max	X - Cable Range	
						Min **	Max
03*	.844 (21.4)	n/a	.562 (14.3)	.843 (21.4)	.630 (16.0)	.156 (4.0)	.250 (6.4)
04*	.844 (21.4)	n/a	.562 (14.3)	.906 (23.0)	.755 (19.2)	.188 (4.8)	.312 (7.9)
06*	.906 (23.0)	n/a	.562 (14.3)	1.093 (27.8)	.942 (23.9)	.281 (7.1)	.438 (11.1)
08	.969 (24.6)	1.312 (33.3)	.562 (14.3)	1.187 (30.1)	1.067 (27.1)	.344 (8.7)	.562 (14.3)
10	.969 (24.6)	1.312 (33.3)	.562 (14.3)	1.281 (32.5)	1.192 (30.3)	.375 (9.5)	.625 (15.9)
12	.969 (24.6)	1.344 (34.1)	.562 (14.3)	1.500 (38.1)	1.380 (35.1)	.438 (11.1)	.750 (19.1)
16	1.062 (27.0)	1.688 (42.9)	.562 (14.3)	1.719 (43.7)	1.535 (39.0)	.562 (14.3)	.938 (23.8)
20	1.125 (28.6)	1.906 (48.4)	.562 (14.3)	2.062 (52.4)	1.848 (46.9)	.750 (19.1)	1.250 (31.8)
24	1.188 (30.2)	1.906 (48.4)	.594 (15.1)	2.312 (58.7)	2.255 (57.3)	.781 (19.8)	1.375 (34.9)
28	1.719 (43.7)	2.125 (54.0)	.594 (15.1)	2.719 (69.1)	2.505 (63.6)	.969 (24.6)	1.625 (41.3)
32*	1.781 (45.2)	n/a	.750 (19.1)	2.969 (75.4)	2.755 (70.0)	1.125 (28.6)	1.875 (47.6)
40*	1.781 (45.2)	n/a	.812 (20.6)	3.531 (89.7)	3.255 (82.7)	1.469 (37.3)	2.375 (60.3)

\* Not available in Style M clamp.

\*\* Not Applicable Style D