



RJ45 CAT 5E ETHERNET COMPATIBLE Series 801, 804 and 805 Mighty Mouse




805-301 Triple-Start Connector with RJ45 Plug (Plug) or Jack (Receptacle) to Crimp Removable Contacts

Series 805 Triple Start


How To Order	
Sample Part Number	805-301 - NF 01 G 21 5H A 1
Series	805-301 = Crimp Contacts
Rear Accessory Option	- = Accessory Thread and Teeth B = Integral Boot Adapter S = Integral Banding Platform
Material and Finish¹	NF = Aluminum/Cadmium, Olive Drab M = Aluminum/Electroless Nickel MT = Aluminum/Nickel PTFE ZNU = Aluminum/Black Zinc Nickel
Shell Style¹	01 = In Line Receptacle 02 = Front or Rear Panel Mount Square Flange Receptacle 12 = Rear Panel Mount Square Flange Receptacle with "Non-Locking" Clinch Nuts 22 = Rear Panel Mount Square Flange Receptacle with "Locking" Clinch Nuts 07 = Rear Panel Mount Jam Nut Receptacle 16 = Plug
Shielding/Grounding²	- = Inline Shielded G = Inline Shielded and Grounded to Shell
Shell Size	21 = Shell Size 21
RJ45 Category	5H = Cat 5E For Cat 6A applications consult factory
Aternate Key Positions¹	A, B, C, D, E, F; A = Normal
RJ45 Orientation Option	1, 2, 3, 4

RJ45 JACK ORIENTATION OPTIONS

▼ = Master Key (Plug)




▼ = Master Keyway (Receptacle)




SHELL STYLE 16 PLUG

RJ45 Plug Category (CAT 5e) Orientation 3 Shown



SHELL STYLE 01 IN-LINE RECEPTACLE

RJ45 Jack Category (CAT 5e) Orientation 3 Shown






RJ45 CAT 5E ETHERNET COMPATIBLE
Series 801, 804 and 805 Mighty Mouse




805-301 Triple-Start Connector with RJ45 Plug (Plug) or Jack (Receptacle) to Crimp Removable Contacts


SHELL STYLE 02 FRONT OR REAR PANEL MOUNT RECEPTACLE



SHELL STYLE 12 & 22 REAR PANEL MOUNT RECEPTACLE WITH CLINCH NUTS




SHELL STYLE 07 REAR PANEL MOUNT JAM NUT RECEPTACLE



REAR ACCESSORY OPTIONS

S - Integrated Banding Platform **B - Integrated Boot Adaptor**



NOTES

1. See Section A for recommended panel cutout dimensions, additional finishes and alternate keyway positions.
2. G option is inline shielded and grounded to shell, receptacle only
3. Meets IP67 sealing requirement in unmated condition
4. Supplied with size 23 crimp pin contacts (809-001 supplied loose)