



For angled part requirements, use in conjunction with Glenair 327-060 Extenders (Page D-5)

TABLE I: CONNECTOR				
Shell Size	Max Entry Code**	Shell Size		
		F/L	H	Max Entry Code**
08	00	08	09	01
10	01	10	11	02
12	02	12	13	03
14	03	14	15	04
16	04	16	17	05
18	05	18	19	06
20	06	20	21	07
22	07	22	23	08
24	08	24	25	09

\*\*Consult factory for additional entry sizes available.

TABLE II: CABLE ENTRY		
Entry Code**	D ±.010 (0.25)	Number of Holes
00	.268 (6.8)	2*
01	.354 (9.0)	2**
02	.472 (12.0)	2**
03	.591 (15.0)	2*
04	.709 (18.0)	2*
05	.837 (21.3)	2*
06	.945 (24.0)	2*
07	1.063 (27.0)	4*
08	1.191 (30.3)	4*
09	1.319 (33.5)	4*

\*Oval Holes, .256 (6.5) x .512 (13.0)  
 \*\*Oval Holes, .315 (8.0) x .512 (13.0)  
 \*Circular Holes, .512 (13.0) Diameter.

TABLE III: FINISH	
<b>XM</b>	2,000 Hr. Corrosion Resistant Electroless Nickel
<b>XW</b>	2,000 Hr. Corrosion Resistant Cad/O.D. over Electroless Nickel
<b>NOTE: Coupling Nut supplied Unplated</b>	

**NOTES:**

- For effective grounding, connector with conductive finish should be used.
- Glenair Series 600 Backshell Assembly Tools are recommended for installation. Consult factory for assembly instructions.
- Metric dimensions (mm) are in parentheses and are for reference only.
- Connector Code H supplied with black coupling nut.