



ArmorLite Stainless Steel Nickel Plated Braid ARM-110/1

1 meter samples	Resistivity (mΩ)	15 inches samples	Resistivity (mΩ)	12 inches samples	Resistivity (mΩ)	6 inches samples	Resistivity (mΩ)	3 inches samples	Resistivity (mΩ)
103-051-002 *	129	103-051-002 *	27.75	103-051-002 *	22.08	103-051-002 *	10.73	103-051-002 *	4.96
103-051-004	96	103-051-004	50.55	103-051-004	40.67	103-051-004	19.92	103-051-004	9.63
103-051-008	65	103-051-008	31.38	103-051-008	25.02	103-051-008	12.23	103-051-008	5.85
103-051-012	48	103-051-012	19.15	103-051-012	15.14	103-051-012	7.36	103-051-012	3.42
103-051-016	33	103-051-016	14.38	103-051-016	11.54	103-051-016	5.53	103-051-016	2.50
103-051-020	26	103-051-020	12.91	103-051-020	10.23	103-051-020	4.93	103-051-020	2.25
103-051-024	23	103-051-024	9.68	103-051-024	7.69	103-051-024	3.70	103-051-024	1.64
103-051-032	13	103-051-032	4.98	103-051-032	4.02	103-051-032	1.93	103-051-032	0.89
103-051-048	8	103-051-048	3.30	103-051-048	2.58	103-051-048	1.32	103-051-048	0.62

* Typical low resistance occurs because of the density of the braid acting similar to a stranded twisted wire.

update 1 mtr 12/28/11